

17.5 x 16mm FL, Grade 1, Double-Convex Lens



Stock **#73-860** CLEARANCE **5 In Stock**

-

1

+

₹866

ADD TO CART

Volume Pricing	
Qty 1+	₹866 each
Need More?	Request Quote

Product Downloads

General

Type:

Double-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

17.50

Optical Properties

Effective Focal Length EFL (mm):

16.00

f/#:

0.91	
	Numerical Aperture NA:
0.55	
Regulatory Compliance	
	Certificate of Conformance:
View	
	Country of Origin:
United States	
	Imported By:
Edmund Optics India Private Limited	

Product Details

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Double-convex (DCX) lenses have two outward curved surfaces, a positive focal length and are useful for 1:1 imaging and in multi-element systems.

15 - 19.9mm Experimental Quality Double-Convex (DCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

Note: Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

Technical Information

