

TECHSPEC®

18mm Dia. x 27mm FL, VIS-NIR Coated, Double-Convex Lens



Stock **#45-883** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

₹4,089.00

ADD TO CART

Qty 1-9
₹4,089.00
Qty 10+
₹3,676.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
18.00 +0.0/-0.025

Back Focal Length BFL (mm):
25.25

Effective Focal Length EFL (mm): 27.00
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870 nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 5.50
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 2.42
Radius R₁=R₂ (mm): 27.08
Clear Aperture CA (mm): 17.00
f/#: 1.5
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.33
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 1000
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View