



TECHSPEC<sup>®</sup> 19.1mm Dia. 400 - 750nm Broadband  $\lambda/10$  Mirror



Stock **#39-205** 8 In Stock

-

1

+

₹7,590

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹7,590 each                   |
| Qty 6-25       | ₹6,072 each                   |
| Qty 26-49      | ₹5,683 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:  
Flat Mirror

Physical & Mechanical Properties

Diameter (mm):  
19.10 +0.00/-0.10

|                         |                       |
|-------------------------|-----------------------|
| Commercial Polish       | Back Surface:         |
| 90                      | Clear Aperture (%):   |
| Ground, 0.5mm max bevel | Edges:                |
| <3                      | Parallelism (arcmin): |
| 6.35 ±0.20              | Thickness (mm):       |

Optical Properties

|                                                                                         |                                |
|-----------------------------------------------------------------------------------------|--------------------------------|
| Dielectric Mirror (400-750nm)                                                           | Coating:                       |
| R <sub>avg</sub> >98% @400 - 750nm (0 - 45°)<br>R <sub>avg</sub> >99% @400 - 750nm (0°) | Coating Specification:         |
| 400 - 750                                                                               | Wavelength Range (nm):         |
| λ/10                                                                                    | Surface Flatness (P-V):        |
| Fused Silica (Corning 7980)                                                             | Substrate: □                   |
| 20-10                                                                                   | Surface Quality:               |
| Dielectric                                                                              | Coating Type:                  |
| 0-45                                                                                    | Angle of Incidence (°):        |
| 0.5 J/cm² @532nm, 20ns, 20Hz                                                            | Damage Threshold, Reference: □ |


Regulatory Compliance

|                                     |                             |
|-------------------------------------|-----------------------------|
| Compliant                           | RoHS 2015:                  |
| Compliant                           | Reach 209:                  |
| View                                | Certificate of Conformance: |
| United States                       | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |

## Product Details

- Enhanced Reflectivity and LIDT over Metallic Coatings
  - Average Reflectivity >99% Over Broad UV, Visible, and NIR Wavelengths
  - Designed for all Polarization States from 0 – 45° AOI
- TECHSPEC® Broadband Dielectric λ/10 Mirrors are ideal for beam steering or reflection applications utilizing multiple laser sources. These mirrors feature greater than 99% reflection, significantly better than metal-coated mirrors, and increase system performance by minimizing energy loss. The highly durable fused silica substrate offers a low thermal expansion coefficient and a high abrasion resistance. TECHSPEC® Broadband Dielectric λ/10 Mirrors are designed for applications from the UV to the near-infrared spectra.

## Technical Information



## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we

provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts

---