

[See all 22 Products in Family](#)

**TECHSPEC® 19.1mm Dia. Laser Mirror Substrate**



TECHSPEC® Laser Mirror Substrates

Stock **#38-000** **20+ In Stock**

MRP ₹10,089

**!** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹10,089 each
Qty 11-25	₹8,929 each
Qty 26-50	₹7,819 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Laser Mirror Substrate      **Type:**

**Physical & Mechanical Properties**

<3      **Parallelism (arcmin):**

**Clear Aperture (%):**

Commercial Polish **Back Surface:**

19.10 +0.00/-0.10 **Diameter (mm):**

6.35 ±0.20 **Thickness (mm):**

Ground, protective bevel as needed **Edges:**

## Optical Properties

10-5 **Surface Quality:**

λ/10 **Surface Flatness (P-V):**

Uncoated **Coating:**

[Fused Silica](#) (Corning 7980) **Substrate:**

## Regulatory Compliance

[Compliant](#) **Reach 191:**

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91-80-6845 0000

## Product Details

- λ/10 and λ/20 Surface Flatness and 10-5 Surface Quality
- High Quality Fused Silica Substrates
- Imperial Sizes with Circular or Rectangular Geometries
- [Window Substrates](#) Also Available

TECHSPEC® Laser Mirror Substrates are manufactured from high quality fused silica and are designed for use with high power laser sources. These mirrors feature excellent surface specifications, including λ/10 and λ/20 surface flatness and 10-5 surface quality, to limit the possibility of reduced performance due to surface defects. The high surface quality of these mirror blanks also makes them ideal for use in demanding intra-cavity laser applications. TECHSPEC Laser Mirror Substrates are available in standard imperial sizes, with either circular or rectangular geometries. Please contact us if your application requires a custom size laser mirror substrate.

## Compatible Mounts