

1mW 780nm Mini LDM Laser Diode Module



Stock #72-810 **1 In Stock**

- 1 + MRP ₹20,072

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-9	₹20,072 each
Qty 10+	₹19,069 each
Need More?	Request Quote

Product Downloads



General

Type:
Index Guided Diode, CW

Mean Time To Failures MTTF @ 25° (hours):
≥90,000

Drive Circuitry:
Fully shielded, reverse polarity protected

Note:
Includes: Users Manual, Warning Label, and Focus Key

Diode **Type of Laser:**

IIIb **Laser Class - CDRH:**

Physical & Mechanical Properties

9.5 **Weight (g):**

<25 **Pointing Accuracy (mrad):**

230 **Length of Leads (mm):**

37.00 **Length (mm):**

Optical Properties

780.00 **Wavelength (nm):**

±10nm **Wavelength Tolerance (nm):**

0.25 **Wavelength Stability (nm/°C):**

<25 **Beam Size at Nearest Focus (µm):**

4 x 2 at Aperture **Beam Diameter (mm):**

<0.5 **Beam Divergence (mrad):**

IR **Color:**

35mm - ∞ **Focus Range (mm):**

Electrical

<50 **Operating Current (mA):**

1 (Maximum) **Output Power (mW):**

±5 **Output Power Tolerance (%):**

Hardware & Interface Connectivity

Power Supply:
Power Supply Required and Sold Separately:
USA: [#59-099](#)
Europe: Not Available
Japan: [#59-099](#)
Korea: Not Available
China: [#59-099](#)

3.5 - 5 VDC **Power Requirement:**

red (+), black (-) **Electrical Leads/ Pin Connections:**

Free Space **Output Type:**

Environmental & Durability Factors

-10 to +55 **Operating Temperature (°C):**

-10 to +85 **Storage Temperature (°C):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 240:**

United Kingdom **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- Line Generation Optics Available
- Bare Leads for Instrument Integration
- Focusable from 35mm to Infinity

Self-contained and miniature, laser diode modules offer a variety of features. They are an ideal replacement for a helium-neon laser in many applications, and offer the benefits of superior durability, small size, and a range of wavelengths and powers. Elliptical output beams are produced using a user-adjustable glass focusing lens. Circular output beams are produced using a long focal length plastic lens and are suitable for long distance and alignment applications. Applications include use as pilot beams for alignment, bar code readers, measurement, dimensional scanning, robotic control, target designation, positioning, and analysis. Focusing tool included with all diode modules. Line Generator attachments are available for all diode modules listed. [Power Supply](#), required for operation, sold separately.

Note: Laser diode case is electrically isolated from supply voltage.

Technical Information

