

1" Travel, Eng Micrometer, Thru-Hole 2.62" Stage



Stock #38-203 1 In Stock

-

1

+

₹96,089

ADD TO CART

Volume Pricing	
Qty 1+	₹96,089 each
Need More?	Request Quote

Product Downloads

General

English

Type:

Thru-Hole

Note:

Physical & Mechanical Properties

Linear (X)

Type of Movement:

Ball Bearing

Guide System:

Drive Orientation:

Center Drive		
66.5 x 66.5	Stage Size (mm):	
1	Travel (inches):	
Aluminum Top and Base/440C Stainless Steel Bearings	Construction:	
0.00005		Graduation (inches):
62	Load Capacity, Normal (lbs):	
10		Load Capacity, T _a (lbs):
2	Load Capacity, T _b (lbs):	
2.62 x 2.62		Stage Size (inches):
0.00008 per inch of travel		Straight Line Accuracy (inches):
1.4		Weight (lbs):

Hardware & Interface Connectivity

Digital Micrometer (English)		Type of Drive:

Regulatory Compliance

Compliant		RoHS 2015:
View		Certificate of Conformance:
United States		Country of Origin:
Edmund Optics India Private Limited		Imported By:


Product Details

- 0.001mm Resolution Directly Readable Micrometer
 - Readout in Inches or Millimeters
 - Available with English or Metric Mounting Holes
- Available with standard (English) or metric mounting holes, these digital micrometers have a precision ground mounting surface and clear LCD readout. The micrometers also feature incremental or absolute positional modes, zero set at any position, inch or millimeter readouts (0.001mm resolution), display hold, and automatic shutdown to conserve the integral battery. Stage travels are one inch and table tops are available with or without a thru-hole.


Technical Information

Figure	Size A	Size B	Size C	Size D	Size E	Size F	Threading G	Threading H	Stock No.
Solid Top									
A	1.75"	0.75"	1.12"	2.12"	1.00"	0.50"	6-32	#6	#53-857
A	1.75"	0.75"	1.12"	2.12"	1.00"	—	6-32	#6	#53-856
A	2.62"	1.00"	2.00"	3.00"	2.00"	—	10-32	#¼	#38-199
A	2.62"	1.00"	2.00"	3.00"	2.00"	1.00"	10-32	#¼	#38-203
B	5.00"	1.00"	4.00"	—	4.00"	—	¼-20	#¼	#38-202
B	5.00"	1.00"	4.00"	—	4.00"	2.00"	¼-20	#¼	#38-204
C	44.4mm	19.0mm	30.0mm	53.8mm	25.0mm	—	M4	M4	#55-461
C	66.5mm	25.4mm	50.0mm	75.9mm	50.0mm	—	M5	M6	#55-462
D	127.0mm	25.4mm	100.0mm	—	—	—	M6	M6	#55-463
D	66.5mm	25.4mm	50.0mm	75.9mm	50.0mm	25.4mm	M5	M6	#55-464


Digital Micrometer Positioning Stage (Figure A)



Digital Micrometer Positioning Stage (Figure B)



Digital Micrometer Positioning Stage (Figure C)



Digital Micrometer Positioning Stage (Figure D)

