

[See all 6 Products in Family](#)

**TECHSPEC® 1X-8X Magnification, NIR I Coated, Adjustable Mounted Anamorphic Prism Pair**



1X-8X Magnification, NIR I Coated, Adjustable Mounted Anamorphic Prism Pair

Stock #34-553 **4 In Stock**

⊖ 1 ⊕ MRP ₹52,463

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹52,463 each
Qty 6-25	₹41,949 each
Qty 26-49	₹39,400 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Beam Shaping **Type:**

**Physical & Mechanical Properties**

52 x 27.7 x 35.6 **Dimensions (mm):**

**Optical Properties**

NIR I (600-1050nm)	<b>Coating:</b>
<b>N-SF11</b>	<b>Substrate:</b> <input type="checkbox"/>
1X-8X (with 1mm Dia. Minor Axis Input Beam)	<b>Magnification:</b>
20-10	<b>Surface Quality:</b>
3	<b>Angle Tolerance (arcmin):</b>
$R_{avg} \leq 0.5\% @ 600 - 1050nm$	<b>Coating Specification:</b>
600 - 1050	<b>Wavelength Range (nm):</b>
$7 J/cm^2 @ 1064nm, 10ns$	<b>Damage Threshold, By Design:</b> <input type="checkbox"/>
3.00	<b>Power (fringes) @ 632.8nm:</b>
1.00	<b>Irregularity (fringes) @ 632.8nm:</b>

## Threading & Mounting

Mounted (Adjustable Magnification)	<b>Mount:</b>
------------------------------------	---------------

## Regulatory Compliance


<a href="#">View</a>	<b>Certificate of Conformance:</b>
China	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91-80-6845 0000	<b>Imported By:</b>

## Product Details


- Converts Elliptical Beam to Circular
- Anti-Reflection Coated for Common Diode Wavelengths
- Mounted and Unmounted Versions Available

An anamorphic prism pair is used to expand a laser beam in one dimension. This makes it ideal for converting the elliptical beam shape of laser diodes into a nearly circular one. Mounting our unmounted anamorphic prism pair in the proper orientation will provide magnification ratios from 2:1 - 6:1. Designed at 650nm and broadband anti-reflection (BBAR) coated for 600 – 1050nm, it provides excellent performance at both 635nm and 670nm.


The center of the output beam is displaced 5.9mm from center of the input beam in our mounted anamorphic prism pair. The Dovetail Accessory Mount allows it to rotate with respect to the laser, simplifying bench-top mounting. The C-Accessory Mount allows our full line of [C-Mount components](#) to be used in conjunction with the mounted anamorphic prism pair.



## Technical Information





Ray path for anamorphic prism pairs, showing transformation of elliptical beam to circular beam



Ray path for mounted variable magnification anamorphic prism pairs, showing entrance and exit apertures on the housing

Typical Values				
Magnification	$\alpha_1$	$\alpha_2$	Vertical Separation (V)	Beam Displacement (D)
2X	-20.6°	-6.5°	1.75mm	4.50mm
3X	-29.7°	-0.9°	2.56mm	5.45mm
4X	-34.1°	2.1°	3.01mm	5.74mm
5X	-37.4°	3.2°	3.33mm	6.15mm
6X	-39.7°	4.0°	3.51mm	6.42mm



### Beam Expander Mounting Configurations.

Click on an item below to be brought to that item's product page.

