

[See all 7 Products in Family](#)

1X SWIR PE IR Plan APO Objective



SWIR Plan APO Infinity Corrected Objective

Stock **#26-217** **1 In Stock**

⊖ 1 ⊕ MRP ₹15,97,248

📌 Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹15,97,248 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

420 Weight (g):

Optical Properties

200.00 Focal Length FL (mm):

1X Magnification:

0.03 Numerical Aperture NA:

22.4	Resolving Power (μm):
611.00	Depth of Field (μm):
Not Available	Cover Glass Correction:
12	Working Distance (mm):
800 - 1600	Wavelength Range (nm):
24.00	Maximum Image Circle (mm):

Threading & Mounting

M26	Mounting Threads:
-----	--------------------------

Regulatory Compliance

View	Certificate of Conformance:
Japan	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- High-Resolution for Short Wave Infrared (SWIR) Wavelengths up to 1600nm
 - Available in Magnifications of 1x to 50X
 - Ideal for Photo Emission Detection, Laser Marking, and Laser Cutting
- SWIR Plan APO Infinity Corrected Objectives are high resolution objective lenses with long working distances that are color corrected between 800 – 1600nm. Available in magnifications of 1X to 50X, these objectives feature high numerical apertures for high resolution imaging at SWIR wavelengths. With a common 95mm parfocal length, these objectives can be combined with a 200mm focal length tube lens and a compatible [C-mount camera](#) for easy system integration. SWIR Plan APO Infinity Corrected Objectives are ideal for Photo Emission Detection, Wafer Backside Inspection, Laser Glass Cutting, and Laser Scan Microscopy applications.