

[See all 2 Products in Family](#)

1mm Dia., Four-Element Segmented InGaAs Photodiode



#17-077, 1mm Dia., Four-Element Segmented InGaAs Photodiode

Stock **#17-077** [CONTACT US](#)

- 1 + ₹26,550

ADD TO CART

Volume Pricing	
Qty 1-4	₹26,550 each
Qty 5-9	₹23,760 each
Qty 10+	₹21,960 each
Need More?	Request Quote

Product Downloads

General	
	Rise/ Fall Time @ V _R =5V (ns):
3 (typical)	
Physical & Mechanical Properties	
	Size of Active Area (mm):
1 Dia.	
	Element Gap (mm):
0.045	

Electrical	
	Responsivity @ 1310nm (AW): 0.85 minimum / 0.9 typical
	Responsivity @ 1550nm (AW): 0.9 minimum / 0.95 typical
	Capacitance @ V_R=5V (pF): 25
	Noise Equivalent Power NEP (W/ Hz^{1/2}): 1.20 x 10 ⁻¹⁴ @ 1550nm
	Maximum Reverse Voltage (V): 15
	Dark Current @ V_R=5V (nA): Maximum: 15 Typical: 0.5
Hardware & Interface Connectivity	
	Connector: TO-5
Environmental & Durability Factors	
	Operating Temperature (°C): -40 to +75
	Storage Temperature (°C): -55 to +125
Regulatory Compliance	
	Certificate of Conformance: View
	Country of Origin: United States
	Imported By: Edmund Optics India Private Limited

Product Details

- Four Individual Active Area Elements
- High Response Uniformity and Low Crosstalk
- Ideal for Position Detection and Beam Alignment
- [Segmented Silicon Photodiodes](#) and [InGaAs Photodiodes](#) Also Available

Segmented InGaAs Photodiodes feature large active areas divided into four individual elements. The four elements of these photodiodes have high response uniformity and low crosstalk, enabling their use in accurate nulling or centering applications. These photodiodes are stable over time and temperature, providing responsivity from 900 - 1700nm with excellent responsivity between 1100 - 1620nm. Segmented InGaAs Photodiodes are ideal for position detection, beam alignment, and beam profiling applications in the near-infrared spectrum. Each photodiode is packaged in an isolated TO-5 or TO-8 can with an antireflection coated window to increase throughput.

Technical Information

