

1mW 515nm Micro LDM Laser Diode Module



Stock **#72-824** **2 In Stock**

- 1 + MRP ₹26,762

i Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-9	₹26,762 each
Qty 10+	₹25,424 each
Need More?	Request Quote

Product Downloads



General

Index Guided Diode, CW **Type:**

Mean Time To Failures MTTF @ 25° (hours):
≥40,000

Drive Circuitry:
Fully shielded, reverse polarity protected

Note:
Includes: Users Manual, Warning Label, and Focus Key

Diode **Type of Laser:**

II **Laser Class - CDRH:**

Physical & Mechanical Properties

3 **Weight (g):**

<25 **Pointing Accuracy (mrad):**

220 **Length of Leads (mm):**

27.40 **Length (mm):**

Optical Properties

515.00 **Wavelength (nm):**

±10nm **Wavelength Tolerance (nm):**

0.25 **Wavelength Stability (nm/°C):**

<40 **Beam Size at Nearest Focus (µm):**

3 x 1 at Aperture **Beam Diameter (mm):**

<0.5 **Beam Divergence (mrad):**

Green **Color:**

50mm - ∞ **Focus Range (mm):**

Electrical

<60 **Operating Current (mA):**

1 **Output Power (mW):**

±5 at 25°C **Output Power Tolerance (%):**

Hardware & Interface Connectivity

+10Vdc power supply required **Power Supply:**

10 VDC **Power Requirement:**

red (+), black (-) **Electrical Leads/ Pin Connections:**

Free Space **Output Type:**

Environmental & Durability Factors

-10 to +45 **Operating Temperature (°C):**

-10 to +85 **Storage Temperature (°C):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 240:**

United Kingdom **Country of Origin:**

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000 **Imported By:**

Product Details

- 7mm Housing Diameter
- Focusable
- Low Voltage DC Operation
- Reverse Polarity Protection

Micro LDM Laser Diode Modules feature an extremely compact design that includes automatic power control circuits and focusable optics. The rugged body is low voltage isolated from the drive electronics, removing the need for negative or floating supplies. It has a highly visible red laser output that can be seen in most daylight conditions. Micro LDM Laser Diode Modules' additional features include aspheric lens, elliptical beam, small output beam diameter, and focused spot size. Meet IEC60825 certification, in accordance with CDRH. Applications include alignment/positioning, bar code readers, dimensional scanning, metrology, event detection, robot control, target designation, edge detection, analysis, and security.

Recommended power supply: [#59-099](#)
