

20 x 20mm, 800μm Pitch, 0.3° Divergence, Cyl. Microlens Array



Stock **#23-873** 3 In Stock

-

1

+

₹43,207

ADD TO CART

Volume Pricing	
Qty 1-10	₹43,207 each
Qty 11-25	₹39,003 each
Qty 26-49	₹36,823 each
Need More?	Request Quote

Product Downloads

General

	Type:
Lens Array	

Physical & Mechanical Properties

	Dimensions (mm):
20.0 x 20.0 ±0.10	
	Radius R (mm):
78.000	

2.00 ±0.1	Thickness (mm):
Optical Properties	
173.50 @ 1064nm	Effective Focal Length EFL (mm):
Fused Silica (Corning 7980)	Substrate: □
Uncoated	Coating:
200 - 2200	Wavelength Range (nm):
0.3 (Full Width)	Divergence Angle (°):
800	Pitch (µm):
Single-Sided	Array Type:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:
Germany	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Generate Non-Gaussian Line Patterns
- Ideal for Light Homogenization
- Excellent Performance from 193nm – 2.5µm

Cylindrical Microlens Arrays are used to homogenize a variety of light sources, including lasers or high power LEDs. Unlike [Square Microlens Arrays](#), which generate spot patterns, Cylindrical Microlens Arrays yield non-gaussian line patterns, and are ideal for welding, drilling, or laser ablation applications from the UV to IR. Cylindrical Microlens Arrays are available uncoated, VIS-NIR, or UV-NIR coated, including options with lenses on a single side for line generation applications or double-sided (with cross-oriented lenses) for beam homogenisation. Additionally, these lenses can be used as fast axis collimators.