

[See all 5 Products in Family](#)

# Photometrics Moment USB 3.2 Camera, 01-MOMENT-MONO



Stock #90-393 **NEW** 1 In Stock

1 MRP ₹6,05,340

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹6,05,340 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

Monochrome

Spectrum:

### General

Monochrome Camera

Type:

01-MOMENT-MONO

Model Number:

Teledyne Photometrics

Manufacturer:

Moment **Camera Series:**

**Note:**  
Includes:  
USB Interface Card  
USB cable  
(2) single-line MMCX trigger cables  
USB memory device containing PVCAM library and drivers  
Quick Installation Guide

## Physical & Mechanical Properties

**Dimensions (mm):**  
40 x 42 x 50

**Weight (g):**  
96

**Housing:**  
Full

## Optical Properties

**Wavelength Range (nm):**  
300 - 1100

## Sensor

**Sensor Format:**  
1.1"

**Resolution (Megapixels):**  
7.00

**Frame Rate (fps):**  
51.00

**Pixels (H x V):**  
3,200 x 2,200

**Sensing Area, H x V (mm):**  
14.4 x 9.9

**Imaging Sensor:**  
Sony-Based

**Type of Sensor:**  
Progressive Scan CMOS

**Shutter Type:**  
Global

**Pixel Depth:**  
12 bit

**Exposure Time:**  
12µs- 1s

**Dynamic Range (dB):**  
72

## Hardware & Interface Connectivity

**Connector:**  
USB 3.2 Gen 2

**Power Supply:**  
Power over USB

**GPIOs:**  
1 configurable input, 1 configurable outputs

**Synchronization:**  
Hardware Trigger (GPIO) or Software Trigger

**Interface Port Orientation:**  
Back Panel

**GPIO Connector Type:**  
BNC

## Threading & Mounting

**Mount:**  
C-Mount

**Mounting Threads:**  
(1) M3 x 0.5 thread per side

## Environmental & Durability Factors

**Operating Temperature (°C):**  
0 to 30

**Storage Temperature (°C):**  
-20 to 60

## Regulatory Compliance

**RoHS 2015:**  
Exempt

Reach 247:

[Contains SVHC\(s\)](#)

Country of Origin:

Canada

Imported By:

Edmund Optics India Private Limited  
 267, Greystone Building, Second Floor,  
 6th Cross Rd, Binnamangala,  
 Stage 1, Indiranagar, Bengaluru,  
 Karnataka, India 560038  
 Phone: +91- 80-6845 0000

## Product Details

- Ultra-Compact CMOS
- Low Noise, High Speed Imaging
- True Global Shutter
- Scientific Cameras for High Sensitivity Microscopy Applications



Teledyne Photometrics Moment USB 3.2 Cameras measure just 50 × 40 × 42 mm and operate with a single high-speed USB 3.2 Gen 2 cable. This allows seamless integration into space-limited microscope systems and complex multi-device workflows. These cameras feature a low-read-noise CMOS sensor coupled with a true global shutter, achieving high-speed imaging at up to 50 fps with 12-bit depth. Teledyne Photometrics Moment USB 3.2 cameras are ideal for demanding applications such as live-cell imaging, light-sheet microscopy, and super-resolution microscopy. These cameras include Teledyne's proprietary-designed software platforms, Beacon and PVCAM, for optimizing camera performance and ease of system integration.


### Scientific Image Quality

The Moment delivers quantitative measurements and optimizes image quality by suppressing hot pixels and patterns common to industrial devices.

Combined with low dark noise and optimized linearity the Moment gives high quality images in low light situations.

### Global Shutter Snapshot

Global shutter minimizes the complexity of illumination control, simplifying your imaging setup. Collect all the light that comes your way without the dead time, artefacts and synchronization issues of a rolling shutter device.



### Ultra-compact Form Factor

Measuring just 50 mm x 40 mm x 42 mm, the Moment is truly compact. Over 3 times smaller than other CMOS devices on the market, the Moment can fit easily into existing instruments, or minimize the footprint of your new device.

### Speed and Simplicity

The Moment utilizes the simple, versatile and high-speed USB 3.2 Gen 2 – 10 GBit/s interface to deliver 50 fps full frame. What's more, both data and power are provided by the same cable, simplifying integration.



### Design and Integrate

Interfacing and integration is simple with the Moment. With its compact design and single cable interface, hardware integration is straightforward. And with onboard triggering, combined with Windows and Linux support, communicating with a camera has never been easier.