

1X 65mm WD, In-Line Illumination 1.2" Telecentric Lens



1.2" Sensor In-Line Illumination Telecentric Lenses

Stock #72-172 **1 In Stock**

⊖ 1 ⊕ MRP ₹3,71,700

● Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | ₹3,71,700 each |
| Need More? | Request Quote |

Product Downloads

General

Product Family:
1.2" Sensor In-Line Illumination Telecentric Lenses

Type:
Telecentric Lens

Compatible Light Guide/Source:
1/4" (0.312")

Type of Illumination:
In-Line Illumination

Physical & Mechanical Properties

| | |
|--------|----------------------------|
| 160.00 | Length (mm): |
| 0.312 | Ferrule Diameter (inches): |
| 19.3 | Maximum Diameter (mm): |

Optical Properties

| | |
|---------|---|
| 14.50mm | Horizontal Field of View @ Max Sensor Format: |
| 8.0mm | Horizontal Field of View, 2/3" Sensor: |
| 6.8mm | Horizontal Field of View, 1/2" Sensor: |
| 19.30 | Maximum Image Circle (mm): |
| 1X | Primary Magnification PMAG: |
| 1.00 | Telecentric Lens Magnification: |
| 65.00 | Working Distance (mm): |
| f/6.0 | Aperture (f/#): |
| <0.01% | Distortion (%): |
| 1X | Magnification: |
| VS | Lens Wavelength Range: |

Sensor

| | |
|------|------------------------|
| 1.2" | Maximum Sensor Format: |
| 2.74 | Pixel Size (µm): |

Threading & Mounting

| | |
|---------|----------------|
| N/A | Filter Thread: |
| C-Mount | Mount: |

Regulatory Compliance

| | |
|---|-----------------------------|
| View | Certificate of Conformance: |
| Japan | Country of Origin: |
| Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000 | Imported By: |

Product Details

- 1.2" Max Sensor Format
- Fiber Optic Input for In-line Illumination
- Long Working Distance

1.2" Sensor In-Line Illumination Telecentric Lenses are designed for cameras with SONY IMX367, 530, and 540 or equivalent sensors allowing for large fields of view. These lenses are designed with an in-line illumination port that accepts a 1/4" fiber optic light guide with incorporated M3 set screws in the in-line illumination port to light guide and include a lockable ring to rotate the lens and ensure alignment with the camera sensor. These telecentric lenses are designed to achieve high coaxial uniformity on 3µm, 24.5MP sensors and reduce parallax errors yielding maximum image quality with an excellent degree of measurement accuracy. 1.2" Sensor In-Line Illumination Telecentric Lenses are available in magnifications ranging from 0.5X–3.45X and offer low f/#s and a low distortion of <0.01%. These lenses are ideal for applications including machine vision, metrology, automotive and electronic inspection, measurement, and gauging.

Note: 1/4" [Fiber optic light guides](#) are sold separately.