

## 1x2 Fiber Coupler, 980nm, 99:1,FC/APC



Stock #75-496 NEW **2 In Stock**

MRP ₹27,400

**●** Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1-4	₹27,400 each
Qty 5-9	₹24,660 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

300 (Max) **Optical Power (mW):**

### General

**Fiber Cable Type:**  
Hi1060 fiber, 900µm loose tube

### Physical & Mechanical Properties

1.00 **Length of Fiber (m):**

## Optical Properties

980.00 **Center Wavelength CWL (nm):**

±15 **Bandwidth (nm):**

1% / 99% (Port 1/Port 2 & 3) **Coupling Ratio:**

## Hardware & Interface Connectivity

FC/APC **Connector:**

19.0 (Port 1 to 2, Max)  
0.9 (Port 1 to 3, Max) **Insertion Loss (dB):**

Max Excess Loss: 0.4 **Loss (dB):**

## Environmental & Durability Factors

-5 to +70 **Operating Temperature (°C):**

-40 to +85 **Storage Temperature (°C):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- 980, 1064, or 1550nm Narrowband Center Wavelength Options Available
- 50:50, 75:25, 90:10, or 99:1 Coupling Ratio Options Available
- FC/APC Connectorized for Easy Integration

1x2 Single Mode (SM) Fiber Splitters/Couplers allow for a single fiber input to be split into two outputs or for multiple inputs to be combined into one output. These narrowband couplers feature center wavelengths of 980, 1064, or 1550nm with coupling ratios of 50:50, 75:25, 90:10, or 99:1. 1x2 Single Mode (SM) Fiber Splitters/Couplers are rated for use in systems with optical powers up to 300mW and are terminated with FC/APC Connectors. These couplers are ideal for applications that require light to be split from a single input into two outputs at a specific, narrow wavelength range and coupling ratio.

**Note:** Please [contact us](#) for Custom Wavelength, Coupling Ratio, and Connector Options.