


[See all 98 Products in Family](#)

200µm Aperture Diameter, 0.5" OD Mounted, Ceramic Aperture



Stock **#90-316** NEW **2 In Stock**

MRP ₹16,244

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹16,244 each
Qty 6+	₹14,457 each
Need More?	Request Quote

Product Downloads

General

Mounted Type:

Physical & Mechanical Properties

12.7 +0.000/-0.05 Outer Diameter (mm):

Construction:

Alumina Ceramic

200 **Fixed Aperture Diameter (μm):**

0.25 Nominal **Thickness (mm):**

± 10 **Aperture Tolerance (%):**

± 125 **Aperture Centration (μm):**

Threading & Mounting

2.54 **Mount Thickness (mm):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 247:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Ceramic, Copper, Gold-Plated Copper, Molybdenum, or Tungsten Substrates
- Withstand High Power Densities up to $130\text{MW}/\text{cm}^2$ (For Mo and W Substrates)
- Ideal for Spatial Filtering and Laser Aperturing

High Power Apertures are available in an assortment of available substrates, making them a versatile option for a variety of laser applications. These products are ideal for spatial filtering and as a general aperture. The apertures have an outer diameter of 3/8" (9.5mm). High Power Apertures have one shiny side for high reflectivity while the other is blackened for absorption. The ceramic apertures are white on both sides. The aperture's thickness and the materials' high reflectivity enable them to withstand and quickly dissipate increased irradiation from high-energy lasers. Densities as high as $100\text{MW}/\text{cm}^2$ ($130\text{MW}/\text{cm}^2$ for molybdenum and Tungsten substrates) have been used without damage to the apertures.