

[See all 85 Products in Family](#)

200 x 200mm Sheet of Metal Velvet Foil, No Adhesive

See More by [Acktar](#)



Acktar Light Absorbent Foil



Stock **#20-047** **9 In Stock**

MRP ₹14,231

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹14,231 each
Need More?	Request Quote

Product Downloads

General

Model Number:
MV-20X20-0

Type:
No Adhesive

Dimensions (cm):
20 x 20

Physical & Mechanical Properties

200 x200 **Dimensions (mm):**

115 **Foil Thickness (µm):**

Optical Properties

Metal Velvet™ **Coating:**

5 - 7 **Coating Thickness (µm):**

0.3 - 14 **Wavelength Range (µm):**

Environmental & Durability Factors

-196 to +350 **Operating Temperature (°C):**

Light, do not touch **Abrasion Resistance:**

ML-C-48497A **Humidity Resistance:**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 247:**

Israel **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Diffusive, Lambertian, or Specular Reflectance
- Extremely Wide Band Performance from the UV to IR
- Standard, Low Outgassing, and No Adhesive Options
- [Die Cut Labels](#) and [Larger Rolls](#) Available

Acktar Light Absorbent Foil and Film is used to eliminate light reflectance in applications where the direct coating of parts is not practical, including optical packaging, laser devices and platforms, IR systems, or passive thermal control. Acktar Light Absorbent Foil and Film features high emissivity with low reflectance, low outgassing, excellent biocompatibility, a broad operating temperature range, and compatibility with class 1 cleanrooms. Acktar Light Absorbent Foil and Film is available in pre-cut patterns or as large sheets for custom patterns.

Acktar Light Absorbent Foil and Film is offered in Metal Velvet™ (diffusive coating on aluminum), Spectral Black™ (semi-specular coating on aluminum), MaxiBlack™ (diffusive coating on polyimide), or Lambertian Black™ (diffusive coating on stainless steel). Metal Velvet offers superior light absorption performance while Spectral Black is more durable, and Lambertian Black performs better at grazing angles. MaxiBlack, in addition to being durable and flexible, is nonconductive and can be used in applications that require light absorbing materials with no electrical conductivity.

Note: Metal Velvet has low resistance to abrasion and all surface contact should be avoided without proper equipment.

Technical Information

Light Absorbing Coatings - Hemispherical Reflectance



Product Type	Metal Velvet™	Lambertian Black™	MaxiBlack™	Spectral Black™	Hexa-Black™
Key Features	Low reflectance of ~1%	High absorption at grazing angles	Thin polyimide, nonconductive substrate	Semi-specular finish	Ultra-high absorption at grazing angles
Substrate Material	Aluminum	Stainless Steel	Polyimide (Kapton)	Aluminum	Aluminum Honeycomb
Substrate Thickness	120μm	100μm	75μm	130μm	2mm
Appearance	Diffusive	Highly Diffusive	Diffusive	Specular	Diffusive 3D Structure
Typical Spectral Range	EUV - FIR	EUV - FIR	UV - MMIR	MS - MMIR	EUV - FIR
AOI Range	0 - 60°	0 - 80°	0 - 60°	0 - 45o	0 - 88°
Reflectance @ 0° AOI	~1%	~1.5%	~2.5%	~2%	~1.5%
Abrasion Resistance	Light	Moderate to High	Moderate	Moderate	Moderate
Cleanliness	Class 10000 - ISO 7	Class 100 - ISO 5	Class 100 - ISO 5	Class 100 - ISO 5	Class 10000 - ISO 7