

[See all 3 Products in Family](#)

20 x 30cm Sheet of Optopolymer® Optical PTFE, 1mm Thick, Adhesive Film



Front



Stock #22-987 **14 In Stock**

1 MRP ₹21,543

 Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-10	₹21,543 each
Qty 11+	₹19,389 each
Need More?	Request Quote

Product Downloads

General

Standard Adhesive **Type:**

20 x 30 **Dimensions (cm):**

Physical & Mechanical Properties

200 x 300
Dimensions (mm):
1.00
Thickness (mm):

Optical Properties

0.25 - 2.5
Wavelength Range (μm):

Environmental & Durability Factors

-200 to +260
Operating Temperature ($^{\circ}\text{C}$):

Regulatory Compliance

[View](#)
Certificate of Conformance:

Germany
Country of Origin:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000
Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume



Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Optical PTFE Material with Lambertian Reflection
- High Reflectance from 250 - 2500nm
- High UV Stability and Chemical Resistance

Optopolymer® Diffuse Reflecting Film consists of optical polytetrafluoroethylene (PTFE) which achieves virtually ideal Lambertian reflectance properties and high reflectance from 250 to 2500nm. The thickness of the polymer layer influences both the flexibility and reflectance of the film with the 1.0mm film providing the best flexibility to reflectance ratio. A 0.5mm thickness provides the best flexibility with a small decrease in reflectance, and a 2.0mm thickness provides the highest reflectance with increased rigidity. Regardless of the thickness, the film can be easily cut to size using scissors and with the adhesive backing and can be tailored to fit any application. Optopolymer® Diffuse Reflecting Film feature high UV stability and universal chemical resistance to minimize discoloration that would result in reflection loss. These reflecting films are ideal for calibration and contrast measurements, projection applications, lining UV sterilizers and photobioreactors, and as reflective diffusers.

Technical Information



Typical, normalized reflectance profile of Optopolymer®, showing near Lambertian properties. The gap in data is due to the detector crossing the path of the incident beam.

