


TECHSPEC[®] 200 x 200mm Linear Polarizing Film (XP42-18)



Stock #86-181 CLEARANCE 10 TO 12 DAYS

-

1

+

₹8,961.00

ADD TO CART

Qty 1-5
₹8,961.00
Qty 6+
₹7,134.00
Volume Pricing
Request Quote

Get Product Downloads

Extinction Ratio:
9000:1 (nominal at 555nm)

Substrate: [Polymer Film XP42-18](#)

Operating Temperature (°C):
-40 to +80

Dimensions (mm):
200.0 x200.0

Thickness (mm): 0.19 ±0.03
Transmission (%): Single: 42 Parallel: 36 Crossed: <0.004 (nominal at 555nm)
Type: Linear Polarizer
Dimensional Tolerance (mm): ±2.0
Construction: Polarizing Film
Note: Polarization axis can be identified as follows: Circular Parts - Parallel to direction of notch on polarizer Square Parts - Parallel to mark on protective film Rectangular Parts - Parallel to first listed dimension
Wavelength Range (nm): 400 - 700
Polarization Efficiency (%): >99.98 (nominal at 555nm)
Heat Resistance (°C x Hours): 80 x 500
#Sorting: 16.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Contains SVHC(s)