

[See all 3 Products in Family](#)

**TECHSPEC® 2000nm Laser Line Mirror, 45° AOI, 12.7mm Dia., 6.35mm Thick**



2µm Laser Line Mirrors

Stock **#27-563** **20+ In Stock**

⊖ 1 ⊕ ₹12,354

**ADD TO CART**

Volume Pricing	
Qty 1+	₹12,354 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Laser Mirror **Type:**

**Physical & Mechanical Properties**

6.35 ± 0.20 **Thickness (mm):**

12.70 +0.00/-0.10 **Diameter (mm):**

90 **Clear Aperture (%):**

Commercial Polish	<b>Back Surface:</b>
<3	<b>Parallelism (arcmin):</b>
<b>Optical Properties</b>	
Fused Silica (Corning 7980)	<b>Substrate:</b> □
10-5	<b>Surface Quality:</b>
Laser Mirror (1900-2200nm)	<b>Coating:</b>
1900 - 2200	<b>Wavelength Range (nm):</b>
λ/10	<b>Surface Flatness (P-V):</b>
<b>Coating Specification:</b>	
R <sub>abs</sub> 99.80% @ 2000nm @ 45° AOI	
R <sub>avg</sub> 99.5% @ 1900 - 2200nm @ 45° AOI	
<b>Regulatory Compliance</b>	
<a href="#">View</a>	<b>Certificate of Conformance:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited	<b>Imported By:</b>

## Product Details

- >99.8% Reflectivity at 2μm
- 99.5% Average Reflectivity in the 1900 - 2200nm Range
- High Laser Damage Threshold
- Wide Range of Laser Line Mirrors Options Available

TECHSPEC® 2μm Laser Line Mirrors are designed with an absolute reflectivity of >99.8% at 2μm at a 45° angle of incidence. These mirrors are manufactured from high quality fused silica and are designed for use with high power laser sources. Available in standard 12.7, 25.4, and 50.8mm sizes, these mirrors can be easily integrated into existing laser systems. TECHSPEC® 2μm Laser Line Mirrors feature λ/10 surface flatness and 10-5 surface quality to ensure reduced scattering in sensitive laser applications. These mirrors are ideal for applications including medical surgery, dermatology, laser doppler velocimetry (LDV), and remote sensing.