

[See all 3 Products in Family](#)

TECHSPEC® 2000nm Laser Line Mirror, 45° AOI, 25.4mm Dia., 6.35mm Thick



2µm Laser Line Mirrors

Stock #27-565 **20+ In Stock**

⊖ 1 ⊕ ₹14,355

ADD TO CART

Volume Pricing	
Qty 1+	₹14,355 each
Need More?	Request Quote

Product Downloads

General

Laser Mirror **Type:**

Physical & Mechanical Properties

6.35 ± 0.20 **Thickness (mm):**

25.40 +0.00/-0.10 **Diameter (mm):**

90 **Clear Aperture (%):**

Commercial Polish	Back Surface:
<3	Parallelism (arcmin):
Optical Properties	
Fused Silica (Corning 7980)	Substrate: □
10-5	Surface Quality:
Laser Mirror (1900-2200nm)	Coating:
1900 - 2200	Wavelength Range (nm):
λ/10	Surface Flatness (P-V):
Coating Specification:	
R _{abs} 99.80% @ 2000nm @ 45° AOI	
R _{avg} 99.5% @ 1900 - 2200nm @ 45° AOI	
Regulatory Compliance	
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- >99.8% Reflectivity at 2μm
- 99.5% Average Reflectivity in the 1900 - 2200nm Range
- High Laser Damage Threshold
- Wide Range of Laser Line Mirrors Options Available

TECHSPEC® 2μm Laser Line Mirrors are designed with an absolute reflectivity of >99.8% at 2μm at a 45° angle of incidence. These mirrors are manufactured from high quality fused silica and are designed for use with high power laser sources. Available in standard 12.7, 25.4, and 50.8mm sizes, these mirrors can be easily integrated into existing laser systems. TECHSPEC® 2μm Laser Line Mirrors feature λ/10 surface flatness and 10-5 surface quality to ensure reduced scattering in sensitive laser applications. These mirrors are ideal for applications including medical surgery, dermatology, laser doppler velocimetry (LDV), and remote sensing.