

[See all 102 Products in Family](#)

TECHSPEC<sup>®</sup> 20.0mm Diameter x 80.0mm FL, 785nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex(PCX) Lenses



Stock **#89-028 6 In Stock**

☐ [Other Coating Options](#)

-

1

+

₹4,204

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | ₹4,204 each                   |
| Qty 10-25      | ₹3,795 each                   |
| Qty 26-49      | ₹3,367 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Plano-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

|                           |                      |
|---------------------------|----------------------|
| 20.00 +0.0/-0.025         |                      |
| Centering (arcmin):       | <1                   |
| Center Thickness CT (mm): | 2.35 ±0.10           |
| Edge Thickness ET (mm):   | 1.13                 |
| Clear Aperture CA (mm):   | 19                   |
| Bevel:                    | Protective as needed |

|                                  |                                   |
|----------------------------------|-----------------------------------|
| Optical Properties               |                                   |
| Effective Focal Length EFL (mm): | 80.00 @ 587.6nm                   |
| Back Focal Length BFL (mm):      | 78.45                             |
| Coating:                         | Laser V-Coat (785nm)              |
| Coating Specification:           | R <sub>abs</sub> <0.25% @ 785nm   |
| Substrate: □                     | N-BK7                             |
| Surface Quality:                 | 40-20                             |
| Power (P-V) @ 632.8nm:           | 1.5λ                              |
| Irregularity (P-V) @ 632.8nm:    | λ/4                               |
| Focal Length Tolerance (%):      | ±1                                |
| Radius R <sub>1</sub> (mm):      | 41.48                             |
| f/#:                             | 4.00                              |
| Numerical Aperture NA:           | 0.12                              |
| Design Wavelength DWL (nm):      | 785                               |
| Damage Threshold, By Design: □   | 5 J/cm <sup>2</sup> @ 785nm, 10ns |

|                             |                                     |
|-----------------------------|-------------------------------------|
| Regulatory Compliance       |                                     |
| RoHS 2015:                  | Compliant                           |
| Certificate of Conformance: | View                                |
| Reach 235:                  | Compliant                           |
| Country of Origin:          | Japan                               |
| Imported By:                | Edmund Optics India Private Limited |

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- <0.25% Reflection at 785nm
- BBAR Coating Options Also Available: [uncoated](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#)
- [405nm](#), [532nm](#), [633nm](#), 785nm, [980nm](#), [1064nm](#), and [1550nm](#) V-Coated Options Offered

TECHSPEC® 785nm Laser Line Coated Plano-Convex (PCX) Lenses are designed for maximum throughput at the specified laser wavelength. These lenses are ideal for collecting and focusing light from laser sources and their corresponding harmonics. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components. TECHSPEC® 785nm Laser Line Coated Plano-Convex (PCX) Lenses are available Laser V-Coated in a range of other wavelengths: [405nm](#), [532nm](#), [633nm](#), [980nm](#), [1064nm](#), and [1550nm](#). Other coating options are available, including [uncoated](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), and [NIR II](#).

## Technical Information



## Coating Curves

## Compatible Mounts