

200µm Aperture Diameter, Ceramic Aperture



Ceramic Aperture

Stock **#84-916** **2 In Stock**

-

1

+

₹9,902

ADD TO CART

Volume Pricing	
Qty 1-5	₹9,902 each
Qty 6-10	₹8,773 each
Qty 11+	₹8,098 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties	
9.5	Outer Diameter (mm):
Alumina Ceramic	Construction:
200	Fixed Aperture Diameter (µm):
0.25 Nominal	Thickness (mm):

±10	Aperture Tolerance (%):
±125	Aperture Centration (µm):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Ceramic, Copper, Gold-Plated Copper, Molybdenum, or Tungsten Substrates
- Withstand High Power Densities up to 130MW/cm² (For Mo and W Substrates)
- Ideal for Spatial Filtering and Laser Aperturing

High Power Apertures are available in an assortment of available substrates, making them a versatile option for a variety of laser applications. These products are ideal for spatial filtering and as a general aperture. The apertures have an outer diameter of 3/8" (9.5mm). High Power Apertures have one shiny side for high reflectivity while the other is blackened for absorption. The ceramic apertures are white on both sides. The aperture's thickness and the materials' high reflectivity enable them to withstand and quickly dissipate increased irradiation from high-energy lasers. Densities as high as 100MW/cm2 (130MW/cm2 for molybdenum and Tungsten substrates) have been used without damage to the apertures.