

**TECHSPEC® 20mm 355nm, Laser Line  $\lambda$ /20 High Tolerance Right Angle Mirror**



Stock #37-650 10 TO 12 DAYS

- 1 + **₹22,881.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| ₹22,881.00                    |
| Qty 6+                        |
| ₹18,314.00                    |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Surface Flatness (P-V):  
 $\lambda$ /20

Substrate:   
[Fused Silica](#) (Corning 7980)

Surface Quality:  
20-10

Length of Legs (mm):

|                                                                                                                               |
|-------------------------------------------------------------------------------------------------------------------------------|
| 20.00                                                                                                                         |
| <b>Dimensional Tolerance (mm):</b><br>+0.00/-0.10                                                                             |
| <b>Coating Specification:</b><br>R <sub>abs</sub> >99.8% @ 355nm @ 45° AOI<br>R <sub>avg</sub> >99.5% @ 351 - 358nm @ 45° AOI |
| <b>Coating:</b><br>Laser Mirror (355nm)                                                                                       |
| <b>Bevel:</b><br>Protective bevel as needed                                                                                   |
| <b>Clear Aperture (%):</b><br>90                                                                                              |
| <b>Design Wavelength DWL (nm):</b><br>355                                                                                     |
| <b>Length of Hypotenuse (mm):</b><br>28.30                                                                                    |
| <b>Type:</b><br>Right Angle Mirror                                                                                            |
| <b>Pyramid Tolerance (arcmin):</b><br>±1                                                                                      |
| <b>Angle Tolerance (arcsec):</b><br>±15                                                                                       |
| <b>Damage Threshold, Reference:</b> <input type="checkbox"/><br>1MW/cm <sup>2</sup> @ 355nm                                   |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 209:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |