

TECHSPEC® 20mm Dia., 2mm Thick, Uncoated, Lithium Fluoride (LiF) Window



Lithium Fluoride (LiF) Windows

Stock #19-727 5 In Stock

-

1

+

₹21,712

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | ₹21,712 each                  |
| Qty 11-25      | ₹19,584 each                  |
| Qty 26-49      | ₹18,484 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                     |
|----------------------------------|---------------------|
| Protective Window                | Type:               |
| Physical & Mechanical Properties |                     |
| Protective as needed             | Bevel:              |
| 90                               | Clear Aperture (%): |

|                   |                          |
|-------------------|--------------------------|
| 18.00             | Clear Aperture CA (mm):  |
| 20.00 +0.00/-0.10 | Diameter (mm):           |
| 2.00 ±0.10        | Thickness (mm):          |
| Fine Ground       | Edges:                   |
| 102.00            | Knoop Hardness (kg/mm²): |
| <3                | Parallelism (arcmin):    |
| 0.33              | Poisson's Ratio:         |
| 64.97             | Young's Modulus (GPa):   |

|                        |                                        |
|------------------------|----------------------------------------|
| Optical Properties     |                                        |
| 97.29                  | Abbe Number (v <sub>d</sub> ):         |
| Random                 | Axis Orientation:                      |
| Uncoated               | Coating:                               |
| 1.392                  | Index of Refraction (n <sub>d</sub> ): |
| Lithium Fluoride (LiF) | Substrate:                             |
| λ/2 @ 632.8nm          | Surface Flatness (P-V):                |
| 60-40                  | Surface Quality:                       |
| 150 - 6000             | Wavelength Range (nm):                 |

|                     |                                                              |
|---------------------|--------------------------------------------------------------|
| Material Properties |                                                              |
| 37                  | Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C): |
| 2.64                | Density (g/cm³):                                             |

|                                     |                             |
|-------------------------------------|-----------------------------|
| Regulatory Compliance               |                             |
| <a href="#">View</a>                | Certificate of Conformance: |
| United States                       | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |


## Product Details

- High Transmission from 150nm - 6µm
- Excellent Vacuum UV (VUV) Transmission
- Low Index of Refraction

Lithium Fluoride (LiF) Windows provide high, flat transmission from 150nm to 6µm. Lithium fluoride has excellent transmission in the vacuum ultraviolet (VUV) wavelength range of 150 - 200nm. Lithium fluoride also has a low index of refraction, allowing these windows to be used without an anti-reflection (AR) coating. Lithium Fluoride (LiF) Windows are ideal for use as UV transmission windows in spectroscopy applications, as a diffracting element in X-ray spectrometry, or as infrared windows for thermal imaging applications.

**Note:** Lithium fluoride is sensitive to thermal shock and is attacked by atmospheric moisture at temperatures above 400°C.

## Technical Information



## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools