


TECHSPEC[®] 20mm Dia. 400 - 750nm Broadband λ /10 ZERODUR[®] Mirror



Stock **#24-025** [CONTACT US](#)

-

1

+

₹11,366

ADD TO CART

Volume Pricing	
Qty 1-5	₹11,366 each
Qty 6-25	₹9,031 each
Qty 26-49	₹8,486 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Flat Mirror

Type:

Physical & Mechanical Properties	
20.00 +0.00/-0.20	Diameter (mm):
Commercial Polish	Back Surface:
Protective as needed	Bevel:
90	Clear Aperture (%):
Ground	Edges:
30	Parallelism (arcsec):
3.00 ±0.20	Thickness (mm):
Optical Properties	
λ/10	Surface Flatness (P-V):
ZERODUR®	Substrate: □
20-10	Surface Quality:
R _{avg} >98% @ 400 - 750nm (0 - 45°) R _{avg} >99% @ 400 - 750nm (0°)	Coating Specification:
Dielectric Mirror (400-750nm)	Coating:
Dielectric	Coating Type:
0-45	Angle of Incidence (°):
400 - 750	Wavelength Range (nm):
0.5 J/cm² @ 532nm, 20ns, 20Hz	Damage Threshold, By Design: □
Material Properties	
0.1	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- ZERODUR® Substrates Provide Near Zero Thermal Expansion
 - Enhanced Reflectivity and LDT over Metallic Coatings
 - UV, Visible, and NIR Reflective Coatings Designed for 0-45° AOI
 - Metallic Coated ZERODUR® Mirrors Also Available
- TECHSPEC® Broadband Dielectric ZERODUR® λ/10 Mirrors combine high reflectivity over broad wavelength ranges with a near zero coefficient of thermal expansion (CTE) making them ideal for laser applications where temperature fluctuations could impact optical performance. The ZERODUR® substrates have a coefficient of thermal expansion (CTE) of ±0.10 x 10⁻⁶/°C, which is an order of magnitude lower than most glass types, including fused silica. Featuring coatings designed for 0-45° AOI and >99% average reflectivity, these dielectric coated mirrors provide higher reflectivity than metal coated mirrors, increasing system throughput by minimizing energy loss. TECHSPEC® Broadband Dielectric ZERODUR® λ/10 Mirrors are ideal for beam steering and beam folding applications from the UV to NIR, including fluorescence microscopy, flow cytometry, and laser communications.

TECHNICAL INFORMATION

UV



VIS



NIR



CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

COMPATIBLE MOUNTS