

[See all 23 Products in Family](#)

200mm Travel, Motorized Linear Stage, Integrated Controller, Rotary Encoder

See More by [Zaber™](#)



#15-288, 200 mm Travel, Motorized Linear Stage, Integrated Controller

Stock **#22-220** 1 In Stock

-

1

+

₹3,26,565

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹3,26,565 each
Need More?	Request Quote

Product Downloads

General	
Metric	Type:
Yes	Encoder:
Yes	Manual Control/ LED Indicators:
Zaber Technologies Inc.	Manufacturer:

Requires a 24-48 VDC power supply and either #15-295 for USB connectivity or #15-297 for RS-232 connectivity. A data cable (#15-296 or #15-299) can be used to daisy chain multiple stages together to control simultaneously.		Note:
2-Phase Stepper	Type of Motor:	
Rotary Quadrature Encoder	Encoder Type:	
Physical & Mechanical Properties		
Linear (X)	Type of Movement:	
Needle Roller Bearing	Guide System:	
45 x 340.4	Stage Size (mm):	
203.2	Travel (mm):	
60 (Unidirectional)	Accuracy (µm):	
<12	Backlash (µm):	
21	Height (mm):	
10	Load Capacity (kg):	
<25	Parallelism (µm):	
<3	Repeatability (µm):	
0.00003 to 26	Speed (mm/s):	
0.46	Weight (kg):	
200 CPR	Encoder Resolution:	
253.60	Total Track (mm):	
Optical Properties		
0.05	Resolution (µm):	
Electrical		
350	Maximum Operating Current (mA):	
Hardware & Interface Connectivity		
Precision Lead Screw	Type of Drive:	
Power Supply Required and Sold Separately. USA: #15-294 Europe: #15-294 Japan: #23-662 Korea: #33-773 China: #15-294	Power Supply:	
USB with #15-295 RS-232 with #15-297	Computer Interface:	
Environmental & Durability Factors		
0 - 50	Operating Temperature (°C):	
Regulatory Compliance		
Compliant	RoHS 2015:	
View	Certificate of Conformance:	
Compliant	Reach 247:	
Canada	Country of Origin:	
Edmund Optics India Private Limited	Imported By:	

Product Details

- High Accuracy, 25mm, 50mm, 100mm, and 200mm Travel Options
- Integrated Mtor and Controller
- Available with Integrated, 200 Counts per Revolution (CPR) Motor Mounted Encoder
- Easily Configurable in X-Y or X-Y-Z Configurations
- Vacuum-Compatible Options

Zaber™ High Precision Motorized Stage Systems are computer-controlled, self-contained linear stages that include a stepper motor and built-in controller. Zaber™ High Precision Motorized Stage Systems can connect directly to a computer's RS-232 port, while the included software provides an easy method for controlling travel distance or position. Additionally, the manual control potentiometer permits smooth manual movement. Encoder versions are available for all travel lengths, with 200 Counts per Revolution (CPR) rotary quadrature encoders integrated into the stepper motor. The integrated rotary encoder provides closed-loop control and slip/stall detection and recovery.

Note: A bottom adapter plate (sold separately) is required for mounting to a standard metric or English breadboard. A 24-48 VDC universal power supply, data cables for daisy chaining, and computer interface cables (USB or RS-232) are sold separately as accessories. Use Top Adapter Plate [#68-644](#) to Mount 70mm TECHSPEC® Stages.

Technical Information


Device Overview / Connectors

Images are shown looking into the device.

Power

1


2




Pin	Description
1	24 - 48 V
2	GND (Note: power supplies ground this pin to AC Earth)

Note: To prevent damage to the device due to static buildup, the device should be properly grounded. The power supplies for X-Series devices are non-isolated and thus ground the device chassis to Earth via the negative terminal of the power supply. If for any reason you are using an isolated power supply, please ensure your device is grounded by connecting the negative terminal of the power connector to AC Earth.

#68-645



#68-644



#68-343

