

TECHSPEC[®] 20mm Dia., 0.56 NA, Uncoated, NIR Aspheric Lens



TECHSPEC[®] Near-Infrared (NIR) Aspheric Lenses

Stock **#13-501** **20+ In Stock**

☐ [Other Coating Options](#)

-

1

+

₹18,995

ADD TO CART

Volume Pricing	
Qty 1-5	₹18,995 each
Qty 6+	₹15,259 each
Need More?	Request Quote

Product Downloads

General	
Aspheric Lens	Type:
Physical & Mechanical Properties	
20.00 +0.00/-0.10	Diameter (mm):
<3	Centering (arcmin):

18	Clear Aperture CA (mm):
3.37	Edge Thickness ET (mm):
7.10 ±0.10	Center Thickness CT (mm):
Protective as needed	Bevel:
Plano	Shape of Back Surface:
Optical Properties	
17.99 @ 780nm	Effective Focal Length EFL (mm):
0.56	Numerical Aperture NA:
14.00	Back Focal Length BFL (mm):
S-LAH64	Substrate: ☐
780	Aspheric Design Wavelength (nm):
1.2λ	Asphere Figure Error, RMS @ 632.8nm:
Uncoated	Coating:
40-20	Surface Quality:
0.90	f/#:
375 - 2100	Wavelength Range (nm):
Infinite	Conjugate Distance:
55.59	Power (diopters):
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Optimized for Applications in the NIR
- Uncoated or AR coated versions available
- Multiple Design Wavelengths Available

TECHSPEC® Near-Infrared (NIR) Aspheric Lenses are optimized to eliminate spherical aberration in the near-infrared. Manufactured from S-LAH64 or N-BK7 substrates and polished through a computer numerical controlled (CNC) process, these aspheric lenses achieve high precision performance across the NIR spectrum. These NIR aspheric lenses include uncoated substrates designed at 780nm with coating options at 350-700nm, 600-1050nm, or 900-1700nm. TECHSPEC® Near-Infrared (NIR) Aspheric Lenses are available with low numerical aperture designs for applications that require beam shape to be maintained as well as high numerical aperture designs for light-gathering applications. For custom designed CNC polished aspheric lenses, please contact us.

Compatible Mounts

