

TECHSPEC[®] 20mm Dia. 515nm 45°, Yb:YAG Laser Line Mirror



Yb:YAG ZERODUR Laser Line Mirrors

Stock **#26-886** **14 In Stock**

-

1

+

MRP ₹18,465

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹18,465 each
Need More?	Request Quote

Product Downloads

General	
Laser Mirror	Type:
Physical & Mechanical Properties	
3.00 +/-0.2	Thickness (mm):
20.00 +0.00/-0.20	Diameter (mm):
90	Clear Aperture (%):

30	Parallelism (arcsec):
Optical Properties	
ZERODUR®	Substrate:
20-10	Surface Quality:
45	Angle of Incidence (°):
Laser Mirror (515nm)	Coating:
515	Design Wavelength DWL (nm):
99.8	Reflection at DWL (%):
509 - 520	Wavelength Range (nm):
λ/10	Surface Flatness (P-V):
Coating Specification: R _{abs} > 99.80% @ 515nm @ 45° AOI R _{avg} > 99.5% @ 509 - 520nm @ 45° AOI	
Dielectric	Coating Type:
Damage Threshold, By Design: 15 J/cm ² @ 515nm, 20ns, 20Hz	

Regulatory Compliance	
View	Certificate of Conformance:
United States	Country of Origin:
Imported By: Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Product Details

- ZERODUR® Substrates Provide Near Zero Thermal Expansion
- >99.8% Reflectivity at Yb:YAG Harmonic Frequencies
- High Laser Damage Threshold Specifications

Yb:YAG ZERODUR Laser Line Mirrors combine the extremely low coefficient of thermal expansion of ZERODUR® substrates with the highly reflective TECHSPEC® Yb:YAG mirror coating. Featuring a coefficient of thermal expansion (CTE) of ±0.10 x 10-6/°C these mirrors are great for applications where the optics will be exposed to fluctuating temperatures. The Yb:YAG coating offers a high laser damage threshold compatible with both pulsed and continuous wave lasers. Yb:YAG ZERODUR Laser Line Mirrors are designed with precision polished substrates with λ/10 flatness and 20-10 surface quality. These mirrors are ideal for laser applications that include laser ablation, welding, drilling, cutting, and sintering.