

[See all 12 Products in Family](#)

TECHSPEC[®] 20mm Dia., Uncoated, Linear Glass Polarizer (XP42)



Stock **#19-643** 9 In Stock

-

1

+

₹10,510

ADD TO CART

Volume Pricing	
Qty 1-9	₹10,510 each
Qty 10+	₹9,342 each
Need More?	Request Quote

Product Downloads

General

Type:

Linear Polarizer

Physical & Mechanical Properties

Diameter (mm):

20.00

Thickness (mm):

2.00 ±0.10

Dimensional Tolerance (mm):

+0.00/-0.20

Laminated Glass Polarizing Film	Construction:
Optical Properties	
Uncoated	Coating:
9000:1 @ 546nm	Extinction Ratio:
XP42 Laminated Between Glass	Substrate: 
42 @ 546nm	Transmission (%):
400 - 700	Wavelength Range (nm):
>99.98 @ 546nm	Polarization Efficiency (%):
Environmental & Durability Factors	
-10 to +55	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:
Japan	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Uncoated and Visible AR Coated Options
 - >99.98% Polarization Efficiency
 - 42% Transmission for Uncoated and 45% Transmission for AR Coated Versions
 - XP42 [Plastic](#) and [Film](#) Also Available
- TECHSPEC® High Contrast Glass Linear Polarizers (XP42) are a high transmission, high efficiency solution that are ideal for a broad range of industrial and laboratory applications. Featuring a >99.98% polarization efficiency and an extinction ratio of 9000:1, these polarizers are constructed with an [XP42 high contrast linear polarizing film](#) laminated between two pieces of optical grade glass. TECHSPEC High Contrast Glass Linear Polarizers (XP42) are available uncoated or with a visible AR coating that provides increased transmission from 425 – 700nm. Typical single filter transmission with randomly polarized incident light is 42% for the uncoated options and 45% for the AR coated options.

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
 - High-precision surface quality and flatness
 - Tight tolerances and complex geometries
 - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).