

TECHSPEC[®] 20mm Dia. x 25mm FL, MgF₂ Coated, Achromatic Doublet Lens



MgF₂ Coated Achromatic Lenses



Stock **#49-932** **20+ In Stock**

[Other Coating Options](#)

-

1

+

₹7,551

ADD TO CART

Volume Pricing	
Qty 1-5	₹7,551 each
Qty 6-25	₹6,072 each
Qty 26-49	₹5,683 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Achromatic Lens		Type:
Physical & Mechanical Properties		
Diameter (mm):		20.00 +0.0/-0.025
Clear Aperture CA (mm):		19.00
Centering (arcmin):		<1
Center Thickness CT (mm):		12.00 ±0.20
Center Thickness CT 1 (mm):		9.50 ±0.10
Center Thickness CT 2 (mm):		2.50 ±0.10
Edge Thickness ET (mm):		8.06
Bevel:		Protective as needed
Optical Properties		
Effective Focal Length EFL (mm):		25.00
Focal Length Tolerance (%):		±1
Back Focal Length BFL (mm):		18.71
Focal Length Specification Wavelength (nm):		587.6
Radius R ₁ (mm):		18.03
Radius R ₂ (mm):		-13.27
Radius R ₃ (mm):		-55.46
Substrate: ☐		N-BAF10 / N-SF6
Surface Quality:		40-20
f/#:		1.25
Numerical Aperture NA:		0.40
Coating:		MgF ₂ (400-700nm)
Coating Specification:		R _{avg} ≤1.75% @ 400 - 700nm
Power (P-V) @ 632.8nm:		1.5λ
Irregularity (P-V) @ 632.8nm:		λ/4
Wavelength Range (nm):		400 - 700
Regulatory Compliance		
RoHS 2015:		Compliant
Reach 224:		Compliant
Certificate of Conformance:		View

PRODUCT DETAILS

- Designed for 0° Angle of Incidence
- Less Than 1.75% Reflectance Per Surface @ 400 - 700nm
- VIS 0° and VIS-NIR Coated Achromats Also Available

TECHSPEC® MgF2 Coated Achromatic Lenses consist of two optical components cemented together to form an achromatic doublet which is computer optimized to correct for on-axis spherical and chromatic aberrations. These lenses feature a single layer of MgF2 which provides less than 1.75% reflectivity from 400 – 700nm. TECHSPEC MgF2 Coated Achromatic Lenses are best for applications involving multi-color (white light) imaging due to their specific doublet lens pairing that enables them to correct the color separation inherent in glass. Having eliminated the problematic chromatic aberrations, achromatic doublet lenses become the most cost-efficient means for polychromatic illumination and imaging.

TECHNICAL INFORMATION



COATING CURVES

CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

COMPATIBLE MOUNTS