


[See all 4 Products in Family](#)

## 20mm Optotune Beam Shifter

See More by [Optotune](#)



Optotune Beam Shifters



Stock #23-851 [CONTACT US](#)

1 MRP ₹1,07,110

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹1,07,110 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Rise Time (ms):  
1.3 (typical)

Settling Time (ms):  
4 (typical)

#### Physical & Mechanical Properties

50.8 x 50.8 x 12      **Dimensions (mm):**

53      **Weight (g):**

## Optical Properties

BBAR (400-680nm)      **Coating:**

0.4 (in x and y)      **Scan Angle (°):**

400 - 680      **Wavelength Range (nm):**

>98% @ 400 - 680nm (0-34° AOI)      **Transmission (%):**

<80nm      **Transmitted Wavefront Error, RMS:**

## Hardware & Interface Connectivity

6-pin FPC      **Connector:**

## Regulatory Compliance

[View](#)      **Certificate of Conformance:**

Slovakia      **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Increase Resolution up to 4X with High Angular Position Accuracy
- Fast Transition Times with Light-Weight and Compact Design
- Optotune ICC-4C-2000 Controller Required ([#23-717](#))

Optotune Beam Shifters accurately tilt a glass window in two axes, resulting in a lateral shift of light which facilitates a resolution increase up to 4X. Utilizing pixel shifting these windows make it possible to capture the full sensor resolution for each color channel by shifting an image a full pixel in X and Y. These windows are mounted in a compact aluminum bracket for easy integration into space constrained systems. Optotune Beam Shifters have an EEPROM containing calibration data for precise open-loop control and include a flex cable for quick connection with the Optotune ICC-4C-2000 controller, [#23-717](#), sold separately. In addition to camera and projection systems, these windows are ideal for non-imaging applications such as optical fiber-coupling, 3D printing, and metrology.