

2.0X, High Resolution Inline Telecentric Lens



Stock **#65-028** 1 In Stock

-

1

+

₹3,19,500

ADD TO CART

Volume Pricing	
Qty 1+	₹3,19,500 each
Need More?	Request Quote

Product Downloads

General	
High Res In-Line Illumination C-Mnt Telecentric Lenses	Series:
Magnification Tolerance %: ±3	Note:
Telecentric Lens	Type:
1/4" (0.312")	Compatible Light Guide/Source:
In-Line Illumination	Type of Illumination:

Physical & Mechanical Properties

250.00	Length (mm):
54	Maximum Diameter (mm):

Optical Properties

4.4mm	Horizontal Field of View, 2/3" Sensor:
11.00	Maximum Image Circle (mm):
0.13	Numerical Aperture NA, Object Side:
5.70	Resolving Power, Image Space (μm):
±1.00	Working Distance Tolerance (mm):
2X	Primary Magnification PMAG:
2.00	Telecentric Lens Magnification:
100.00	Working Distance (mm):
f/8 - Closed	Aperture (f/#):
≤0.05	Distortion (%):
2X	Magnification:
VIS	Lens Wavelength Range:

Sensor

2/3"	Maximum Sensor Format:
2.60	Pixel Size (μm):

Threading & Mounting

N/A	Filter Thread:
C-Mount	Mount:

Regulatory Compliance

View	Certificate of Conformance:
Japan	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Designed for High Resolution Imaging
- In-line Illumination Port (0.312" Ferrule)
- 2/3" Max. Sensor Format

This line of high resolution telecentrics was designed to allow of in-line illumination. This make them ideal for applications that need intense and direct illumination. The coaxial port accepts ¼" fiber bundles with a 0.312" ferrule diameter, which readily connects to our wide selection of light guides and illuminators.

The lenses feature a standard C-Mount threading to connect to the most common 2/3" and smaller machine vision cameras. Designed to have =0.05% distortion, these lenses are perfect for challenging measurement applications.