

[See all 164 Products in Family](#)

TECHSPEC<sup>®</sup> 20mm Dia. x 60mm FL, VIS 0° Inked, Double-Convex Lens



Stock **#63-617-INK** [CONTACT US](#)

☐ [Other Coating Options](#)

-

1

+

₹4,995

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | ₹4,995 each                   |
| Qty 10-24      | ₹4,478 each                   |
| Qty 25-99      | ₹4,005 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Double-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

20.00 ±0.025

|                      |                                  |
|----------------------|----------------------------------|
| <1                   | Centering (arcmin):              |
| Protective as needed | Bevel:                           |
| 4.00                 | Center Thickness CT (mm):        |
| ±0.10                | Center Thickness Tolerance (mm): |
| 2.36                 | Edge Thickness ET (mm):          |
| 19.00                | Clear Aperture CA (mm):          |

Optical Properties

|                                      |                                                       |
|--------------------------------------|-------------------------------------------------------|
| 58.67                                | Back Focal Length BFL (mm):                           |
| 60.00                                | Effective Focal Length EFL (mm):                      |
| VIS 0° (425-675nm)                   | Coating:                                              |
| R <sub>avg</sub> ≤0.4% @ 425 - 675nm | Coating Specification:                                |
| N-BK7                                | Substrate: <input type="checkbox"/>                   |
| 40-20                                | Surface Quality:                                      |
| 1.5λ                                 | Power (P-V) @ 632.8nm:                                |
| λ/4                                  | Irregularity (P-V) @ 632.8nm:                         |
| 61.33                                | Radius R <sub>1</sub> =R <sub>2</sub> (mm):           |
| 3.00                                 | f/#:                                                  |
| 587.6                                | Focal Length Specification Wavelength (nm):           |
| ±1                                   | Focal Length Tolerance (%):                           |
| 0.17                                 | Numerical Aperture NA:                                |
| 425 - 675                            | Wavelength Range (nm):                                |
| 5 J/cm <sup>2</sup> @ 532nm, 10ns    | Damage Threshold, By Design: <input type="checkbox"/> |

Regulatory Compliance

|                                     |                             |
|-------------------------------------|-----------------------------|
| View                                | Certificate of Conformance: |
| Japan                               | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |

## Product Details

- AR Coated to Provide <0.4% Reflectance per Surface for 425 - 675nm
- Minimize Aberrations Including Spherical and Coma
- [UV Fused Silica DCX Lenses](#) Available
- Other Coating Options Available: [Uncoated](#), [MgF<sub>2</sub>](#), [NIR I](#), [NIR II](#), [VIS-EXT](#), [VIS-NIR](#), and [YAG-BBAR](#)

TECHSPEC® VIS 0° Coated Double-Convex (DCX) Lenses, also referred to as bi-convex lenses, have two positive, symmetrical faces with equal radii on both sides. These lenses are generally recommended for finite imaging applications with a conjugate ratio (ratio between object distance and image distance) between 0.2 and 5. At a conjugate ratio of 1, aberrations such as spherical aberration, chromatic aberration, coma, and distortion are minimized or cancelled due to the symmetric lens design. TECHSPEC® VIS 0° Coated Double-Convex Lenses are available in a variety of substrates and coating options for the visible and NIR spectra.

## Technical Information



N-BK7

Uncoated N-BK7 Typical Transmission



Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra.

[Click Here to Download Data](#)

N-BK7 with MgF<sub>2</sub> Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$  (N-BK7)

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

N-BK7 with VIS-EXT Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{avg} \leq 0.5\% @ 350 - 700\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

N-BK7 with VIS-NIR Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{abs} \leq 0.25\% @ 880\text{nm}$

$R_{avg} \leq 1.25\% @ 400 - 870\text{nm}$

$R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



Typical transmission of a 3mm thick N-BK7 window with MS 0° (425-675nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{\text{avg}} \leq 0.4\% \text{ @ } 425 - 675\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{\text{abs}} \leq 0.25\% @ 532\text{nm}$$
$$R_{\text{abs}} \leq 0.25\% @ 1064\text{nm}$$
$$R_{\text{avg}} \leq 1.0\% @ 500 - 1100\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{\text{avg}} \leq 0.5\% \text{ @ } 600 - 1050\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{\text{abs}} \leq 1.5\% \text{ @ } 750 - 800\text{nm}$$
$$R_{\text{abs}} \leq 1.0\% \text{ @ } 800 - 1550\text{nm}$$
$$R_{\text{avg}} \leq 0.7\% \text{ @ } 750 - 1550\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

# Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts

---