

TECHSPEC® 20X, VIS-NIR Vega® Broadband Beam Expander



TECHSPEC® Vega™ Broadband Beam Expanders

Stock **#39-741** 10 TO 12 DAYS

- 1 + **₹67,651.00**

ADD TO CART

Qty 1-9
₹67,651.00
Qty 10+
₹59,508.00
Volume Pricing
Request Quote

Get Product Downloads



Angle of Incidence (°):
0

Coating:
Laser VIS-NIR (500-1090nm)

Design Wavelength DWL (nm):
Broadband

Entrance Aperture (mm): 4.5
Exit Aperture (mm): 31.5
Expansion Power: 20X
Substrate: ☐ Fused Silica (Corning 7980)
Length (mm): 128.61
Mounting Threads: Input: Male M30 x 1 Output: Female M27 x 0.5
Transmission (%): >94.0 (nominal)
Type: Beam Expander
Weight (g): 436
Housing Diameter (mm): 48.00
Transmitted Wavefront, P-V: λ/10 for 1.1mm input beam (nominal, λ = DWL)
Coating Specification: R _{avg} ≤ 1.5% @ 500 - 1090nm @ 0° AOI
Wavelength Range (nm): 500 - 1090
Style: Fixed Magnification
Damage Threshold, By Design: ☐ 2 J/cm² @ 1064nm, 20ns, 20Hz
Divergence Adjustment: Rotating Optics

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View