

[See all 19 Products in Family](#)

## 22.2mm Aperture UV/VIS Fiber Optic Collimator, FC



Stock **#17-569** **5 In Stock**

-

1

+

₹47,700

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | ₹47,700 each                  |
| Qty 11-24      | ₹42,300 each                  |
| Qty 25-49      | ₹39,600 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General              |  |
|----------------------|--|
| Type:                |  |
| Fiber Collimator     |  |
| Compatible Fiber NA: |  |
| 0.22                 |  |
| Housing Material:    |  |
| Stainless Steel      |  |

|                                                                                                                                                   |                                     |
|---------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------|
| <div>Note:</div> <div>Compatible with <a href="#">#17-573</a>, <a href="#">#17-574</a>, &amp; <a href="#">#17-575</a> Refocusing Assemblies</div> |                                     |
| Physical & Mechanical Properties                                                                                                                  |                                     |
| 28.58                                                                                                                                             | Diameter (mm):                      |
| 22.2                                                                                                                                              | Aperture Size:                      |
| 52.83                                                                                                                                             | Length (mm):                        |
| Optical Properties                                                                                                                                |                                     |
| <a href="#">Fused Silica</a> (Corning 7980)                                                                                                       | Substrate: <input type="checkbox"/> |
| 190 - 1250                                                                                                                                        | Wavelength Range (nm):              |
| 800 - 1000                                                                                                                                        | Fiber Diameter (µm):                |
| 38.00                                                                                                                                             | Focal Length FL (mm):               |
| Hardware & Interface Connectivity                                                                                                                 |                                     |
| FC                                                                                                                                                | Connector:                          |
| Environmental & Durability Factors                                                                                                                |                                     |
| -40 to 100                                                                                                                                        | Operating Temperature (°C):         |
| Regulatory Compliance                                                                                                                             |                                     |
| <a href="#">View</a>                                                                                                                              | Certificate of Conformance:         |
| United States                                                                                                                                     | Country of Origin:                  |
| Edmund Optics India Private Limited                                                                                                               | Imported By:                        |



## Product Details

- Can Be Coupled to Standard 0.22 NAFiber Optic Cables
- Options Available for UV-VIS or VIS-NIR
- Multiple Focal Length or Aperture Options


Focusable Collimators consist of two separate components: a fiber optic collimator and a fiber optic refocusing assembly. The fiber optic collimator utilizes a PCX lens positioned at the focal length from the optical fiber tip. These collimators are available with FC or SMA threads, and easily couple to standard 0.22 NA fiber optic cables. Focusable Collimators expand the beam and decrease the divergence by the ratio of the fiber core diameter to the collimator aperture. Fiber optic refocusing assemblies mount directly to the fiber optic collimator and allow for optimal focus at a given distance.



## Technical Information



Fiber with 10mm Aperture Fiber Optic Collimator and Refocusing Assembly



A 10mm Aperture Refocusing Assembly can then be directly threaded onto the 10mm Aperture Fiber Optic Collimator.

| Collimator Description                            | Stock Number | Compatible Refocusing Assembly                         |
|---------------------------------------------------|--------------|--------------------------------------------------------|
| 4mm Aperture UV/MS Fiber Optic Collimator, FC     | #88-189      | No Compatible Refocusing Assemblies                    |
| 4mm Aperture UV/MS Fiber Optic Collimator, SMA    | #88-173      | No Compatible Refocusing Assemblies                    |
| 4mm Aperture VIS/NIR Fiber Optic Collimator, FC   | #88-188      | No Compatible Refocusing Assemblies                    |
| 4mm Aperture VIS/NIR Fiber Optic Collimator, SMA  | #88-172      | No Compatible Refocusing Assemblies                    |
| 10mm Aperture UV/MS Fiber Optic Collimator, FC    | #88-191      | #88-182, #88-183, #88-184, #88-185, #88-186, & #88-187 |
| 10mm Aperture UV/MS Fiber Optic Collimator, SMA   | #88-181      | #88-182, #88-183, #88-184, #88-185, #88-186, & #88-187 |
| 10mm Aperture VIS/NIR Fiber Optic Collimator, FC  | #88-190      | #88-182, #88-183, #88-184, #88-185, #88-186, & #88-187 |
| 10mm Aperture VIS/NIR Fiber Optic Collimator, SMA | #88-180      | #88-182, #88-183, #88-184, #88-185, #88-186, & #88-187 |