

[See all 19 Products in Family](#)

## 22.2mm Aperture UV/VIS Fiber Optic Collimator, SMA



Fiber Optic Collimator, SMA (SMA adapter inserted)



Stock #17-567 **7 In Stock**

⊖ 1 ⊕ MRP ₹58,819

ⓘ Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹58,819 each
Qty 11-24	₹52,161 each
Qty 25-49	₹48,831 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Fiber Collimator **Type:**  
0.22 **Compatible Fiber NA:**

Housing Material:  
Stainless Steel

Note:  
Compatible with #17-573, #17-574, & #17-575  
Refocusing Assemblies

## Physical & Mechanical Properties

Diameter (mm):  
28.58

Aperture Size:  
22.2

Length (mm):  
52.83

## Optical Properties

Substrate:   
Fused Silica (Corning 7980)

Wavelength Range (nm):  
190 - 1250

Fiber Diameter (µm):  
800 - 1000

Focal Length FL (mm):  
38.00

## Hardware & Interface Connectivity

Connector:  
SMA

## Environmental & Durability Factors

Operating Temperature (°C):  
-40 to 100

## Regulatory Compliance

Certificate of Conformance:  
[View](#)


Country of Origin:  
United States

Imported By:  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000


## Product Details

- Can Be Coupled to Standard 0.22 NA Fiber Optic Cables
- Options Available for UV-VIS or VIS-NIR
- Multiple Focal Length or Aperture Options

Focusable Collimators consist of two separate components: a fiber optic collimator and a fiber optic refocusing assembly. The fiber optic collimator utilizes a PCX lens positioned at the focal length from the optical fiber tip. These collimators are available with FC or SMA threads, and easily couple to standard 0.22 NA fiber optic cables. Focusable Collimators expand the beam and decrease the divergence by the ratio of the fiber core diameter to the collimator aperture. Fiber optic refocusing assemblies mount directly to the fiber optic collimator and allow for optimal focus at a given distance.




## Technical Information




The 4mm Aperture Fiber Optic Collimator threads directly onto FC or SMA fiber.

**Fiber with 10mm Aperture Fiber Optic Collimator**



Each 10mm Aperture Fiber Optic Collimator includes an FC or SMA adapter that is inserted into the collimator and locked by a set screw.

**Fiber with 10mm Aperture Fiber Optic Collimator and Refocusing Assembly**



A 10mm Aperture Refocusing Assembly can then be directly threaded onto the 10mm Aperture Fiber Optic Collimator.

Collimator Description	Stock Number	Compatible Refocusing Assembly
4mm Aperture UV/MS Fiber Optic Collimator, FC	<a href="#">#88-189</a>	No Compatible Refocusing Assemblies
4mm Aperture UV/MS Fiber Optic Collimator, SMA	<a href="#">#88-173</a>	No Compatible Refocusing Assemblies
4mm Aperture VIS/NIR Fiber Optic Collimator, FC	<a href="#">#88-188</a>	No Compatible Refocusing Assemblies
4mm Aperture VIS/NIR Fiber Optic Collimator, SMA	<a href="#">#88-172</a>	No Compatible Refocusing Assemblies
10mm Aperture UV/MS Fiber Optic Collimator, FC	<a href="#">#88-191</a>	<a href="#">#88-182</a> , <a href="#">#88-183</a> , <a href="#">#88-184</a> , <a href="#">#88-185</a> , <a href="#">#88-186</a> , & <a href="#">#88-187</a>
10mm Aperture UV/MS Fiber Optic Collimator, SMA	<a href="#">#88-181</a>	<a href="#">#88-182</a> , <a href="#">#88-183</a> , <a href="#">#88-184</a> , <a href="#">#88-185</a> , <a href="#">#88-186</a> , & <a href="#">#88-187</a>
10mm Aperture VIS/NIR Fiber Optic Collimator, FC	<a href="#">#88-190</a>	<a href="#">#88-182</a> , <a href="#">#88-183</a> , <a href="#">#88-184</a> , <a href="#">#88-185</a> , <a href="#">#88-186</a> , & <a href="#">#88-187</a>
10mm Aperture VIS/NIR Fiber Optic Collimator, SMA	<a href="#">#88-180</a>	<a href="#">#88-182</a> , <a href="#">#88-183</a> , <a href="#">#88-184</a> , <a href="#">#88-185</a> , <a href="#">#88-186</a> , & <a href="#">#88-187</a>