


20mm Diameter IR Cut-Off Filter



Stock #55-236 **20+ In Stock**

MRP ₹4,792

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-24	₹4,792 each
Qty 25-49	₹4,314 each
Need More?	Request Quote

Product Downloads

General

IR Cut-Off Filter **Type:**

Physical & Mechanical Properties

20.00 ±0.25 **Diameter (mm):**

1.10 ±0.25 **Thickness (mm):**

Clear Aperture (%):

≥90

Edges:

Ground

Optical Properties

710.00 **Cut-Off Wavelength (nm):**

BOROFLOAT®

Substrate:

Traditional Coated **Coating:**

1.472 **Index of Refraction (n_d):**

80-50 **Surface Quality:**

Coating Specification:
Surface 1: T=50% @ 710±30nm, T_{avg}>85% @ 480 - 680nm, T_{avg}<10% @ 740 - 1200nm
Surface 2: N4 MgF₂

480 - 1200 **Wavelength Range (nm):**

Environmental & Durability Factors

<250 **Operating Temperature (°C):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 247:**

United States **Country of Origin:**


Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- 710nm Cut-Off Wavelength
- Circular and Rectangular Options
- Various Sizes Available

IR Cut-Off Filters are ideal for eliminating illumination beyond the visible spectrum in many visual and detector-based applications. These filters feature a 710nm cut-off wavelength. IR Cut-Off Filters are traditionally coated and have a BOROFLOAT® substrate. BOROFLOAT® is about three times more resistant to thermal shock than standard soda lime glass. IR Cut-Off Filters are available in circular and rectangular versions with various sizes for each.

Technical Information



Quote Your Size

Compatible Mounts

