

25° Diffusing Angle, 5mm Sq., Wide Angle Diffuser



Stock **#23-876** **5 In Stock**

-

1

+

₹23,900

ADD TO CART

Volume Pricing	
Qty 1-10	₹23,900 each
Qty 11-25	₹21,487 each
Qty 26-49	₹20,319 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type:

Flat Top Diffuser

Note:

Recommended M²>10 and beam size >2.5mm

FW/e² for best homogeneity and steep slopes

Physical & Mechanical Properties

4.5 x4.5	Clear Aperture CA (mm):
5.00 x5.00 ±0.1	Dimensions (mm):
0.50 ±0.05	Thickness (mm):

Optical Properties

25	Diffusing Angle (°):
Uncoated	Coating:
Fused Silica	Substrate: □
90	Transmission (%):
1064	Design Wavelength DWL (nm):

Regulatory Compliance

View	Certificate of Conformance:
------	-----------------------------

PRODUCT DETAILS

- 25 and 125° Diffusing Angles Available
- 90% Transmission Efficiency
- Eye-Safe ROE, No Zero-Order and No Hot Spot

Wide Angle Diffusers are used to create diffused top hat beam profiles in one dimension and are available in angles of 25 or 125°. These diffusers can be easily paired for diffusion in two dimensions for square or rectangular output profiles with a steep edge slope and high homogeneity. These diffusers have increased transmission efficiency and uniformity versus standard ground glass diffusers. Wide Angle Diffusers are an eye-safe refractive optical element (ROE) with no zero-order and no hot spots. These diffusers are ideal for integration into LIDAR, heads up displays (HUDs), time of flight, 3D sensing, and machine vision applications.

Note: These are designed for use with collimated light with a minimum beam size of 2.5mm FW/e². Use with diverging beams or beam arrays will change output profiles.