

[See all 69 Products in Family](#)

TECHSPEC<sup>®</sup> 25mm Square x 1.1mm Thickness, MgF<sub>2</sub> Coated, BOROFLOAT<sup>®</sup> Window

See More by [SCHOTT Optical Components](#)



TECHSPEC BOROFLOAT Borosilicate Windows

Stock **#29-403** **20+ In Stock**

-

1

+

MRP ₹2,727

 Price inclusive of all taxes

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹2,727 each                   |
| Qty 6-25       | ₹2,185 each                   |
| Qty 26-99      | ₹2,056 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Protective Window

Type:

Glass

Type of Window:

Physical & Mechanical Properties

|                      |                          |
|----------------------|--------------------------|
| 22.50 x22.50         | Clear Aperture CA (mm):  |
| 25.00 x25.00 ±0.50   | Dimensions (mm):         |
| 1.10 ±0.2            | Thickness (mm):          |
| 25.00                | Length (mm):             |
| 25.00                | Width (mm):              |
| Protective as needed | Bevel:                   |
| ≥90                  | Clear Aperture (%):      |
| Ground and Seamed    | Edges:                   |
| 0.20                 | Poisson's Ratio:         |
| 64                   | Young's Modulus (GPa):   |
| 480.00               | Knoop Hardness (kg/mm²): |

Optical Properties

|                    |                                        |
|--------------------|----------------------------------------|
| MgF2 (400-700nm)   | Coating:                               |
| <b>BOROFLOAT®</b>  | Substrate: □                           |
| 1.472              | Index of Refraction (n <sub>d</sub> ): |
| 80-50              | Surface Quality:                       |
| ≥95                | Transmission (%):                      |
| 65.41              | Abbe Number (v <sub>d</sub> ):         |
| Rabs ≤2.5% @ 550nm | Coating Specification:                 |
| 400 - 700          | Wavelength Range (nm):                 |
| 4 - 6λ             | Surface Flatness (P-V):                |

Material Properties

|      |                                  |
|------|----------------------------------|
| 2.23 | Density (g/cm³):                 |
| 525  | Transformation Temperature (°C): |

|                      |                                                              |
|----------------------|--------------------------------------------------------------|
| 3.25 (+20 to +300°C) | Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C): |
|----------------------|--------------------------------------------------------------|

Environmental & Durability Factors

|                                                                  |                                           |
|------------------------------------------------------------------|-------------------------------------------|
| 1 hour @ 500; >100 hours @ 450                                   | Operating Temperature (°C):               |
| Short Term, 1 hr: 110K 1 - 100 hrs: 90K Long Term, >100 hrs: 80K | Resistance to Temperature Difference (K): |
| Up to 4mm Thick: 175K 4 - 6mm Thick: 160K 6 - 15mm Thick: 150K   | Thermal Shock (K):                        |

Regulatory Compliance

|                                                                                                                                                                             |                             |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------|
| <b>Compliant</b>                                                                                                                                                            | RoHS 2015:                  |
| <b>View</b>                                                                                                                                                                 | Certificate of Conformance: |
| <b>Compliant</b>                                                                                                                                                            | Reach 247:                  |
| United States                                                                                                                                                               | Country of Origin:          |
| Edmund Optics India Private Limited<br>267, Greystone Building, Second Floor,<br>6th Cross Rd, Binnamangala,<br>Stage 1, Indiranagar, Bengaluru,<br>Karnataka, India 560038 | Imported By:                |


## Product Details

- Low Coefficient of Thermal Expansion
- Visible to Near Infrared Transmission
- High Resistance to Thermal Shock

TECHSPEC® BOROFLOAT® Borosilicate Windows are ideal for high temperature and harsh environment applications. The windows have a low coefficient of thermal expansion of 3.25 (+20 to +300°C). TECHSPEC® BOROFLOAT® Borosilicate Windows feature visible to near infrared transmission. Unlike common borosilicate that is drawn flat, BOROFLOAT® is produced by a float technique that yields superior surface flatness — typically 4 - 6λ per inch. BOROFLOAT® is about three times more resistant to thermal shock than standard soda lime glass.

Can't find what you need? Get a quick [custom quote](#).

## Technical Information



## Coating Curves

## Quote Your Size

## Compatible Mounts