


TECHSPEC® 100mm Dia. λ /10 ZERODUR® Uncoated Mirror Substrate



Stock #71-524

CONTACT US

-

1

+

₹32,386

ADD TO CART

Volume Pricing	
Qty 1+	₹32,386 each
Need More?	Request Quote

Product Downloads

General	
Mirror Substrate	Type:
Physical & Mechanical Properties	
100.00 +0.00/-0.20	Diameter (mm):
10.00 ±0.20	Thickness (mm):
Commercial Polish	Back Surface:
	Bevel:

Protective as needed	
90	Clear Aperture (%):
Ground	Edges:
30	Parallelism (arcsec):

Optical Properties

Uncoated	Coating:
$\lambda/10$	Surface Flatness (P-V):
ZERODUR®	Substrate: ☐
20-10	Surface Quality:

Material Properties

0.1	Coefficient of Thermal Expansion CTE ($10^{-6}/^{\circ}\text{C}$):
-----	--

Regulatory Compliance

View	Certificate of Conformance:
Vietnam	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Precision ZERODUR® Substrates
- $\lambda/10$ Flatness
- Low Coefficient of Thermal Expansion

TECHSPEC® ZERODUR Mirror Substrates are well suited for applications where temperature fluctuation is a concern. The ZERODUR® substrates have a coefficient of thermal expansion (CTE) of $\pm 0.10 \times 10^{-6}/^{\circ}\text{C}$, which is an order of magnitude lower than most glass types. The low CTE allows these mirrors to have a consistent reflected wavefront, even when exposed to environments with varying temperature or illumination sources with changing intensity. TECHSPEC® ZERODUR Mirror Substrates feature precision polished substrates with $\lambda/10$ flatness and 20-10 surface quality.