


[See all 20 Products in Family](#)

25 x 25mm, 0.125mm Spacing, Glass Distortion Target



Stock #58-509 [CONTACT US](#)

1 MRP ₹86,022

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-4	₹86,022 each
Qty 5+	₹81,795 each
Need More?	Request Quote

Product Downloads

General

Chrome on Glass

Type:

NIST Certification:
Serialized NIST Traceable Certificate Included

Physical & Mechanical Properties

Dot Diameter (mm):

0.0625

Dot Spacing (mm):

0.125

Overall Accuracy (mm):

±0.002

Pattern Size (mm):

25 x 25

Dimensions (inches):

2 x 2

Thickness (mm):

1.50

Dot Diameter Tolerance (mm):

± 0.002

Dot Spacing Tolerance (mm):

± 0.002 Center to Center

Flatness (inches):

0.001

Optical Properties

Coating:

Reflective First Surface Chromium
R_{abs} = 50% ±5% @ 550nm

Substrate: □

Soda Lime Float Glass

Optical Density OD (Average):

>3.0

Surface Quality:

40-20

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 240:

[Compliant](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- For Distortion Measurement and Calibration of Imaging Systems
- Chrome on Soda Lime Glass or Chrome on White Ivory Glass Versions
- NIST Certificate of Accuracy Included

Fixed Frequency Grid Distortion Targets are used to resolve the often-troublesome distortion factor in measurement applications. It is important to note that no information about the object is actually lost, but merely misplaced in the image when distortion occurs. Using these targets, one can easily determine the precise amount of distortion present and back it out of measurements. The dot center can be located using blob (or centroid) analysis in measurement software. Fixed Frequency Grid Distortion Targets are available in various options each with different dot size/dot frequency combinations. Choose a target based on your field of view or resolution/accuracy requirements. These targets are available in either a chrome on soda lime glass or chrome on white ivory glass to accommodate transmission or reflection-based applications, respectively. Included in the packaging is a serialized NIST Traceable Certificate of Accuracy per MIL-STD-45662A.