

**TECHSPEC®**

**20mm H x 20mm L x 50mm FL VIS 0° Coated, Illumination Grade PCX Cylinder Lens**



Stock #25-496 **5 In Stock**

- 1 + MRP ₹13,199

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹13,199 each
Qty 6-25	₹11,956 each
Qty 26-49	₹11,287 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Cylinder Lens, Plano-Convex **Type:**

**Physical & Mechanical Properties**

6.00 ±0.1 **Center Thickness CT (mm):**

**Dimensional Tolerance (mm):**

+0.0/-0.2

20.0 x 20.0 **Dimensions (mm):**

3.99 **Edge Thickness ET (mm):**

±0.1 over H **Tilt Tolerance (mm):**

15.00 **Wedge Tolerance (arcmin):**

## Optical Properties

50.00 **Effective Focal Length EFL (mm):**

N-BK7 **Substrate:** □

2.5 **f#:**

0.20 **Numerical Aperture NA:**

VIS 0° (425-675nm) **Coating:**

350 - 2200 **Wavelength Range (nm):**

46.04 **Back Focal Length BFL (mm):**

R<sub>avg</sub> ≤ 0.4% @ 425 - 675nm **Coating Specification:**

±3 **Focal Length Tolerance (%):**

25.84 **Radius R<sub>1</sub> (mm):**

60-40 **Surface Quality:**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

China **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- N-BK7 Substrate for Broadband Performance
- Cost-Effective for OEM Integration
- Multiple Coating Options Available

TECHSPEC® Illumination Grade PCX Cylinder Lenses are similar to Plano-Convex (PCX) lenses in profile, but include a portion of a cylinder instead of a sphere. These lenses focus light in one dimension and can transform a point of light into a line. TECHSPEC® Illumination Grade PCX Cylinder Lenses are available in circular and rectangular versions, along with multiple coating options. Cylinder lenses are ideal for line projection in machine vision applications or guidance systems.

**Note:** For negative focal length cylinder lenses, see our [TECHSPEC® Illumination Grade PCV Cylinder Lenses](#).





**PCX Rectangular**

Circular And Rectangular Cylinder Lenses



**PCX Circular**

## Coating Curves