


TECHSPEC<sup>®</sup> 20mm NIR II Coated, BBAR Coated Right Angle Prism



Stock #26-776 5 In Stock

-

1

+

₹10,980

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹10,980 each                  |
| Qty 6-25       | ₹8,820 each                   |
| Qty 26-49      | ₹8,280 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

SPECIFICATIONS

General

Right Angle Prism

Type:

Coating on Entrance/Exit Faces

Note:

| Physical & Mechanical Properties                                                                                                           |                                     |
|--------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------|
| +0.00/-0.10                                                                                                                                | Dimensional Tolerance (mm):         |
| Protective as needed                                                                                                                       | Bevel:                              |
| 90                                                                                                                                         | Clear Aperture (%):                 |
| 28.30                                                                                                                                      | Length of Hypotenuse (mm):          |
| 20.00                                                                                                                                      | Length of Legs (mm):                |
| Optical Properties                                                                                                                         |                                     |
| ±15                                                                                                                                        | Angle Tolerance (arcsec):           |
| NIR II (750-1550nm)                                                                                                                        | Coating:                            |
| N-BK7                                                                                                                                      | Substrate: <input type="checkbox"/> |
| 40-20                                                                                                                                      | Surface Quality:                    |
| Left-Handed                                                                                                                                | Image Orientation:                  |
| Coating Specification:<br>R <sub>abs</sub> ≤1.5% @ 750 - 800nm R <sub>abs</sub> ≤1.0% @ 800 - 1550nm R <sub>avg</sub> ≤0.7% @ 750 - 1550nm |                                     |
| 90                                                                                                                                         | Ray Deviation (°):                  |
| 750 - 1550                                                                                                                                 | Wavelength Range (nm):              |
| Damage Threshold, Reference: <input type="checkbox"/><br>Entrance/Exit Faces: 8 J/cm <sup>2</sup> @ 1064nm, 10ns                           |                                     |
| 1.25                                                                                                                                       | Power (fringes) @ 632.8nm:          |
| 0.25                                                                                                                                       | Irregularity (fringes) @ 632.8nm:   |
| Regulatory Compliance                                                                                                                      |                                     |
| Compliant                                                                                                                                  | RoHS 2015:                          |
| View                                                                                                                                       | Certificate of Conformance:         |
| Compliant                                                                                                                                  | Reach 235:                          |


## PRODUCT DETAILS

- Ideal for Low Power Laser Sources
- Multiple BBAR Coatings Available
- Ray Deviation of 90°

TECHSPEC® Broadband Anti-Reflection (BBAR) Coated Right Angle Prisms are ideal for a range of low power laser line applications. These prisms feature tight angle tolerances and a precision N-BK7 substrate. The BBAR coating improves transmission efficiency when compared to uncoated right angle prisms. TECHSPEC® Broadband Anti-Reflection (BBAR) Coated Right Angle Prisms have their BBAR coating on entrance and exit faces. The prisms are available in lengths from 5 to 50mm.

Right angle prisms are generally used to bend image paths or redirect light at 90°. This produces a left-handed image and depending on the orientation of the prism, the image may be inverted or reverted. Right angle prisms can also be used in combination for image/beam displacement.

## TECHNICAL INFORMATION



*Right Angle Prism Ray Path*



*Right Angle Prism Ray Path*



*Right Angle Prism Tunnel Diagram*



*Right Angle Prism Tunnel Diagram*

## CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

---