

TECHSPEC[®] 25 x 35.36 x 1mm NIR, Elliptical Plate Beamsplitter



Elliptical Plate Beamsplitters

Stock #48-916 20+ In Stock

-

1

+

₹18,000

ADD TO CART

Volume Pricing	
Qty 1-5	₹18,000 each
Qty 6-25	₹16,200 each
Qty 26+	₹14,400 each
Need More?	Request Quote

Product Downloads

General	
Standard Beamsplitter	Type:
Physical & Mechanical Properties	
>80	Clear Aperture (%):
Plate	Construction:

	Edges:
Cut with 0.25mm maximum edge chip	
	Major Axis (mm):
36.36 +0.0/-0.70 (physical length)	
	Minor Axis (mm):
25.00 +0.0/-0.10	
	Parallelism (arcmin):
<1	

	Thickness (mm):
1.00 ±0.1	

Optical Properties

	Coating:
NIR	
	Coating Specification:
Surface 1: 50R/50T (R _{abs} ±5% @ 900nm, R _{avg} ±10% @ 700 - 1100nm)	
Surface 2: R _{avg} ≤1.0%, R _{abs} ≤2.0% @ 700 - 1100nm	

	Reflection/Transmission Ratio (R/T):
50/50	
	Substrate: ☐
N-BK7	

	Surface Flatness (P-V):
<2λ (per inch)	
	Surface Quality:
60-40	

	Wavelength Range (nm):
700 - 1100	

Regulatory Compliance

	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	

	Reach 247:
Compliant	

	Country of Origin:
United States	
	Imported By:
Edmund Optics India Private Limited	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Circular Profile at 45°
- Visible and NIR Coating Options Offered
- Ideal for Diffuse Axial and In-line Illumination

TECHSPEC® Elliptical Plate Beamsplitters maximize beamsplitting efficiency while minimizing required mounting space. These beamsplitters are ideal for diffuse axial and in-line illumination. When oriented at 45°, the beamsplitters create a circular aperture equal to the diameter of the minor axis. TECHSPEC® Elliptical Plate Beamsplitters are available with either a visible or NIR 50% reflection/50% transmission beamsplitter coating and feature a high efficiency multi-layer anti-reflection (AR) coating to reduce back reflections. The beamsplitters are offered in either a 1 or 3mm thickness, in a range of major and minor axis measurements and wavelength ranges.

Technical Information



