

**TECHSPEC® 25.0mm Dia., 3.00mm Thick, 532nm,  $\lambda/10$  Fused Silica Window**



TECHSPEC  $\lambda/10$  Laser Line Coated Windows

Stock #48-209 **6 In Stock**

1  MRP ₹17,455

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹17,455 each
Qty 6-25	₹13,923 each
Qty 26-49	₹13,116 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Laser Line Window **Type:**

Glass **Type of Window:**

**Physical & Mechanical Properties**

**Thickness (mm):**

3.00 ±0.10	<b>Clear Aperture CA (mm):</b>
22.50	
	<b>Diameter (mm):</b>
25.00 +0.00/-0.10	
	<b>Clear Aperture (%):</b>
90	
	<b>Parallelism (arcsec):</b>
≤5	
	<b>Bevel:</b>
Protective as needed	
	<b>Edges:</b>
Fine Ground	

## Optical Properties

	<b>Substrate:</b> <input type="checkbox"/>
<b>Fused Silica</b> Excimer Grade (Coming 7980 KrF)	
	<b>Index of Refraction (n<sub>d</sub>):</b>
1.458	
	<b>Surface Quality:</b>
10-5	
	<b>Angle of Incidence (°):</b>
0	
	<b>Coating:</b>
Laser V-Coat (532nm)	
	<b>Design Wavelength DWL (nm):</b>
532	
	<b>Transmitted Wavefront, P-V:</b>
λ/10	
	<b>Abbe Number (v<sub>d</sub>):</b>
67.8	
	<b>Coating Specification:</b>
R <sub>abs</sub> <0.25% @ 532nm	
	<b>Damage Threshold, By Design:</b> <input type="checkbox"/>
10 J/cm <sup>2</sup> @ 532nm, 20ns, 20Hz	
	<b>Damage Threshold, Pulsed:</b>
10 J/cm <sup>2</sup> @ 532nm, 20ns, 20Hz	

## Material Properties

	<b>Fused Silica Grade:</b>
7980 KrF 0A	

## Regulatory Compliance

<b>Compliant</b>	<b>RoHS 2015:</b>
<b>Compliant</b>	<b>REACH 201:</b>
<b>View</b>	<b>Certificate of Conformance:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details




- 10-5 Surface Quality
- Damage Thresholds at Design Wavelengths

- Diameters from 12.5 to 76.2mm Available

- [Uncoated Substrates Available](#)

TECHSPEC® M10 Laser Line Coated Windows are designed for direct integration into laser applications. This robust product family features common imperial sizes, many of which offer multiple thickness options. Anti-reflection coatings are available at common laser wavelengths, minimizing surface reflection for optimal system transmission. TECHSPEC M10 Laser Line Coated Windows provide laser grade specifications including M10 surface flatness, 10-5 surface quality, and <math><3</math> arcmin parallelism. These windows are ideal for industrial laser applications ranging from protective coverings to separating various environments.

## Technical Information



## Compatible Mounts