

[See all 12 Products in Family](#)

20X T0.7 Mitutoyo LC Plan Apo NIR Infinity Corrected Objective

See More by [Mitutoyo](#)



Stock **#23-598** **3 In Stock**

-

1

+

₹4,32,390

ADD TO CART

Volume Pricing	
Qty 1+	₹4,32,390 each
Need More?	Request Quote

Product Downloads

General	
378-821-16	Model Number:
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm	
Microscope Objective	Type:
Infinity Corrected	Style:


Mitutoyo		Manufacturer:
0.7mm thick LCD cover-glass Example Application: High magnification inspection through liquid crystal glass (LCD) or cutting and trimming of semiconductor wafer and circuits		Note:
Physical & Mechanical Properties		
75.00	Length excluding Threads (mm):	
34	Maximum Diameter (mm):	
305.00	Weight (g):	
Optical Properties		
0.7	Compatible Cover Glass Thickness (mm):	
532, 1064	Design Wavelength DWL (nm):	
0.32mm	Horizontal Field of View, 1/2" Sensor:	
0.44mm	Horizontal Field of View, 2/3" Sensor:	
10.00	Focal Length FL (mm):	
20X	Magnification:	
0.40	Numerical Aperture NA:	
0.7	Resolving Power (μm):	
1.70	Depth of Field (μm):	
1.2	Field of View, 24 Diameter Field Eyepiece (mm):	
0.9	Field of View, 18 Diameter Field Eyepiece (mm):	
20.00	Working Distance (mm):	
480 - 1800	Wavelength Range (nm):	
95.37	Parfocal Length (mm):	
N/A	Immersion Liquid:	
Sensor		
2/3"	Maximum Sensor Format:	
Threading & Mounting		
M26 x36 TPI	Mounting Threads:	
Environmental & Durability Factors		
23 ±2	Performance Assurance Temperature (°C):	
Regulatory Compliance		
Exempt	RoHS 2015:	
View	Certificate of Conformance:	
Contains SVHC(s)	REACH 241:	
Japan	Country of Origin:	
Edmund Optics India Private Limited	Imported By:	

Product Details

- Ideal for Brightfield Imaging and Laser-Based Applications through LCD Glass
- Excellent Performance at Nd:YAG Laser Lines
- Compensate for Cover-Glass Thickness of 0.7mm or 1.1mm

Mtutoyo NIR, NUV, and UV LCD Infinity Corrected Objectives combine the benefits of the standard MPlan Apo and MPlan Apo SL series objectives with enhanced spectral ranges. The NIR objectives are corrected from 480 to 1800nm, making them ideal for semiconductor and telecommunication inspection, or for laser cutting with common Nd:YAG lasers. The HR series offers an increased numerical aperture, providing smaller spot sizes and higher resolution. Mtutoyo NIR, NUV, and UV LCD Infinity Corrected Objectives compensate for common LCD glass thicknesses. The NUV and UV series of objectives have excellent performance at the second, third, and fourth Nd:YAG harmonics of 532nm, 355nm, and 266nm respectively.

Technical Information



Units: mm

Dimensions				
M Plan NIR	A (mm)	B (mm)	C (mm)	W.D. (mm)
20X, T0.7	75.00	34	32.2	20.0
20X, T1.1	75.02	34	32.2	19.98
50X, T0.7	78.04	34	32.2	17.26
50X, T0.7 HR	77.74	34	32.2	9.60
50X, T1.1	77.87	34	32.2	17.13
100X	82.94	34	32.2	12.06
HR 100X	85.13	39	37	9.87
M Plan NUV	A (mm)	B (mm)	C (mm)	W.D. (mm)
20X, T0.7	78	34	32.2	16.96
50X, T0.7	80	34	32.2	14.76
100X, T1.1	83.97	34	32.2	11.03
M Plan UV	A (mm)	B (mm)	C (mm)	W.D. (mm)
20X, T0.7	80	34	32.2	14.98
50X, T0.7	83	34	32.2	12.38