

[See all 10 Products in Family](#)

2.15" White, LED Darkfield Illuminator

See More by [Advanced Illumination](#)



Stock #66-790 **1 In Stock**

MRP ₹44,604

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹44,604 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

RL2115-WHI-24	Model Number:
50,000	LED Lifetime (hours):
15.00	Number of LEDs:
	Number of Channels:

1.00

LED Illuminator

Type of Illumination:

Note:

Requires a 24V power supply [#66-855](#). European power supply [#35-200](#) also available.

Advanced Illumination

Manufacturer:

Ring Light

Geometry:

Constant

Illumination Mode:

Physical & Mechanical Properties

19.0

Height (mm):

19.0

Inner Diameter (mm):

55.0

Outer Diameter (mm):

6.4 - 12.7

Field Coverage (mm):

Optical Properties

White

Color:

19 - 25.4

Working Distance (mm):

Electrical

30.00

Maximum Trigger Frequency (Hz):

Hardware & Interface Connectivity

Flying Leads

Connector:

Power Supply Required and Sold Separately:

USA: [#66-855](#)

Europe: [#66-855](#)

Japan: [#89-513](#)

Korea: [#33-773](#)

China: [#66-855](#)

Threading & Mounting

Standard

Mount:

M3 x2

Mounting Threads:

Environmental & Durability Factors

0 to +65

Operating Temperature (°C):

Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Compliant](#)

Reach 233:

United States

Country of Origin:

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Ideal for Visually Enhancing Surface Defects
- Useful for Front or Back Illumination
- 5" Versions Have Variable Intensity

Advanced Illumination Darkfield LED Illuminators are ideal for visually enhancing surface defects. LED intensity can be varied through the in line potentiometer. The 5" darkfield illuminator includes a mounting bracket for easy system integration.

Note: Required 24V power supply [#66-855](#). [Accessories for Advanced Illumination products](#) are available and sold separately.

The strobed models' flash duration is dependent on a trigger signal or potentiometer setting. The duration of the strobe can be adjusted from 30 - 300 μ s via a knob located in the back of the unit. Trigger input signal is CMOS/TTL compatible. The maximum trigger frequency is 30Hz.

3D-Printable Mount Files




Ring Light Configuration

**DOWNLOAD
NOW**

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is based on mounting illumination to 1/4-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.



Application Note

Illumination Mounts for Machine Vision Applications
[Read](#) 



Video

Assembly of 3D Printed Mounts for Common Illumination Geometries
[Watch](#) 