

TECHSPEC® 25 x 25mm 80R/20T, VIS Plate Beamsplitter



Visible and NIR Plate Beamsplitters

Stock **#68-423** **3 In Stock**

MRP ₹18,967

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹18,967 each
Qty 6-25	₹14,831 each
Qty 26-99	₹13,621 each
Need More?	Request Quote

Product Downloads

General

Note:
Beamsplitter-coated side is marked with a black dot

Type:
Standard Beamsplitter

Physical & Mechanical Properties

Clear Aperture (%):

>85

Construction:

Plate

Dimensions (mm):

25.0 x 25.0 +0.0/-0.25

Edges:

Cut with 0.25mm maximum edge chip

Parallelism (arcmin):

≤3

Thickness (mm):

3.00 ±0.25

Optical Properties

Angle of Incidence (°):

45

Coating Specification:

Surface 1: 80/20 ±5% @ 550nm, ±10% @ 400 -

700nm

Surface 2: AR $R_{avg} \leq 1\%$, $R_{abs} \leq 2\%$ @ 400 - 700nm

Reflection/Transmission Ratio (R/T):

80/20

Substrate:

N-BK7

Surface Flatness (P-V):

1λ per inch

Surface Quality:

60-40

Wavelength Range (nm):

400 - 700

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 247:

Compliant

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details


- Many Beamsplitting Ratios Available
- Visible and NIR Coating Options Offered
- Multi-Layer AR Coated Second Surface
- [C-Mounted Plate Beamsplitters](#) Also Available

TECHSPEC® Visible and NIR Plate Beamsplitters are ideal for dual magnification [imaging](#) systems and for combining low power [laser](#) beams. These beamsplitters offer the optimum combination of polished, high-quality optical-grade glass with minimum substrate thickness. The broadband dielectric coatings provide maximum throughput, are ideal for minimizing ghost images, and have much less energy loss than metallic coatings. TECHSPEC® Visible and NIR Plate Beamsplitters are coated on their back surfaces with a multi-layer anti-reflection (AR) coating, reducing back reflections to less than 1.0% for each wavelength range. Note that for easy identification, the coated side of the beamsplitter is marked with a black dot.

Technical Information



**VIS AR Back-Surface
Coating Performance at 45 Degrees**



Compatible Mounts