

[See all 10 Products in Family](#)

25 x 25mm UV Polarizing Film



Stock **#25-111** **4 In Stock**

1 MRP ₹5,397

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹5,397 each
Qty 10-25	₹4,278 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Protective Film on Both Sides **Note:**

Physical & Mechanical Properties

25.00 **Length (mm):**

Dimensions (mm):

25.0 x 25.0 ±0.2

0.19 Nominal **Thickness (mm):**

Polarizing Film **Construction:**

25.00 **Width (mm):**

Optical Properties

Uncoated **Coating:**

1000:1 (avg @ 325nm-400nm)
6000:1 (avg @ 400nm-750nm) **Extinction Ratio:**

CTA (Cellulose Triacetate) **Substrate:**

320 - 750 **Wavelength Range (nm):**

39 (325nm-400nm) **Transmission, Single (%):**

0.04 (325nm-400nm) **Transmission, Crossed (%):**

Environmental & Durability Factors

Heat Resistance: 70°C dry
Cold Resistance: -20°C **Operating Temperature (°C):**

DIN ISO 9022-2-10-04
DIN ISO 9022-2-11-05
DIN ISO 9022-2-12-07
DIN ISO 9022-2-14-02 **Environmental Durability:**

15 - 25 **Storage Temperature (°C):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 251:**

Germany **Country of Origin:**

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000 **Imported By:**

Product Details

- High UV Transmission from 325 - 400nm
- 1000:1 Contrast From 325 - 400nm, 6000:1 Contrast From 400 - 750nm
- Thin, Versatile Polymer Substrate

Ultraviolet (UV) Linear Polarizing Film provides excellent contrast, and transmission up to 39% for P-Polarized Light in the UV and VIS ranges from 325-750nm. A range of rectangular sizes are available to accommodate small and large beam diameters as well as LED light sources. Ultraviolet (UV) Linear Polarizing Films are made with a durable, robust film substrate that is flexible and can be cut to size using scissors. This polarizing film is a cost-effective alternative to glass UV polarizers, and are ideal for use in industrial sensing, spectroscopy, and microscopy applications. [Near-Infrared \(NIR\) Linear Polarizing Film](#) and Visible [TECHSPEC High Contrast Linear Polarizing Film \(XP42\)](#) are also available.