

[See all 5 Products in Family](#)

## 25.0/25.4mm Optic Dia., Low Wavefront Distortion, Top Adjust Kinematic Mount, 2-Screws



Stock #28-750 **3 In Stock**

- 1 + MRP ₹48,629

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹48,629 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Circular **Type of Optics:**

2XTop **Number of Adjustment Screws:**

#### Physical & Mechanical Properties

24.4 **Clear Aperture CA (mm):**

**Construction:**  
Stainless Steel Plates, Stainless Steel Screws, and  
Brass Thread Bushings

25.40 **Optical Axis Height (mm):**

## Threading & Mounting

25.00 - 25.40 **Size of Compatible Optics (mm):**

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Country of Origin:**  
United States

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Low Wavefront Distortion Mounting
- Lockable 100 TPI Fine Adjustment Screws for High Precision and Long-Term Stability
- Space Efficient Rear Adjustment and Top Adjustment Versions

Ultraprecision Kinematic Mounts are designed to provide precise and accurate adjustment of high-end optical components, offering long-term pointing stability and minimizing wavefront distortion. The optic is located in the mounting seat via three contact points, but is secured in place by a retaining spring that gently contacts the leading edge of the optic at three discrete locations to ensure low wavefront distortion, preserving optical flatness and accuracy. These kinematic mounts feature two hex-driven high accuracy adjustment screws (100TPI), that can be easily locked, ensuring long term stability under shock, vibration, and gradient temperature conditions. Ultraprecision Kinematic Mounts are compact in footprint and are available in both standard rear- and top-adjustment configurations, with the top adjust versions being extra space efficient for compact system integration. These mounts are highly configurable, featuring multiple counterbore holes, threaded holes, and dowel pin holes for locating and securing the mounts in any benchtop or OEM application.

## Technical Information

